



1. MATERIAL: ALNICO 5, CAST OR SINTERED
2. MAGNETIZATION LEVEL: SATURATED
TYPICAL VALUE WITH F.W. BELL 4048 GAUSS METER
IS 1400 GAUSS WITH TRANSVERSE PROBE PLACED
ON THE END OF THE MAGNET.
3. MAGNETIZATION DIRECTION: PARALLEL TO LENGTH
4. DIMENSIONS: ARE IN INCHES
5. SQUARENESS: 1°
6. PACKING: PREFERRED METHOD IS 100 MAGNETS SHRINK WRAPPED ON CARDBOARD FLATS.
OTHER METHODS MAY BE ACCEPTABLE WITH APPROVAL.
MAXIMUM WEIGHT IS 25 Lbs. PER BOX.

H-32 MAGNET

H A M L I N, Inc.

DCR No.

AC	CORRECT DRAWING	A7280	JC	7/16/98	JC	7/17/98	Dwn. FH	DATE 1/12/64	250-70-209
REV.	DESCRIPTION OF REVISION	DCR No.	BY	DATE	APP.	DATE	App'd	DATE	Page 1 of 1