



	NIC
PARI	INC.

15-03 TSS RG58 CABLE 50 OHM

REVISIONS								
ECN#	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	Α	RELEASED	Sreejesh	16/1/10	Jagan	16/1/10	Farnell	29/1/10





## Stripping Dimension

## **Specifications**

Bodies : Brass per JIS-C3604 Center contact : Brass per JIS-C3604

Insulation Teflon per ASTM D1457 and ASTM D1710

Connector Interface per MIL-STD-348A
Part to be clean and free of burrs

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from regigence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell pic 2009.

TOLERANCES:	DRA
UNLESS OTHERWISE	Sree
SPECIFIED,	CHE
DIMENSIONS ARE	Jaga
FOR REFERENCE PURPOSES ONLY	APP

DRAWN BY:	DATE:
Sreejesh	16/1/2010
CHECKED BY:	DATE:
1	16/1/2010
Jagan	10/1/2010
APPROVED BY:	DATE:

	DRAWI	NG TITLE:					
)	TNC PLUG- 50 OHM						
)	size <b>A</b>	DWG NO.	M10002421	l .	TRONIC FILE 97-DWG		REV A
	SCALE: NTS		U.O.M.: mm		SHEET: 1	OF	- 2

Dimensions: Millimetres



PART	NO
	IVO.

15-03 TSS RG58 CABLE 50 OHM

REVISIONS								
ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	А	RELEASED	Sreejesh	16/1/10	Jagan	16/1/10	Farnell	29/1/10

## **Specifications Table**

Description	Material	Quantity	Finish
Shell	Brass		Silver 70μ inches (minimum)
Insulation	Teflon		None
Gasket I	Silicone		Red
Body			Silver 70μ inches (minimum)
Washer I	Brass		None
Braid clamp		1	Silver 70μ inches (minimum)
Gasket II	Silicone		Red
Washer II			
Nut	Brass		Silver 70μ inches (minimum)
Center contact	7		

## **Part Number Table**

Description	Part Number		
Plug, TNC, 50R	15-03 TSS RG58 Cable 50 OHM		

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from engligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or strength of the production of the

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

TOLERANCES:

	DRAWN BY:	DATE:	
	Sreejesh	16/1/2010	
	CHECKED BY:	DATE:	
	Jagan	16/1/2010	
	APPROVED BY:	DATE:	
	Farnell	29/01/10	

	DRAW	NG TITLE:				
0			TNC PLUG- S	50 OF	HM	
0	size <b>A</b>	DWG NO.	M10002421	l .	TRONIC FILE 97-DWG	REV A
	SCALE: NTS		U.O.M.: mm		SHEET: 2 O	 F 2