




THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



**AAVID
THERMALLOY**

EUROPE www.aavidthermalloy.com

Via XXV Aprile, 32
40057 Cadrilano - Bologna ITALY
Tel. +39 051 764011
Fax +39 051 764090

Cheney Manor
SWINDON WILTS SN2 2QN UK
Tel. +44 1793 401400
Fax +44 1793 615396

COMPANY
WITH QUALITY SYSTEM
CERTIFIED BY DNV
ISO 9001

COMPANY
WITH QUALITY SYSTEM
CERTIFIED BY BSI
ISO 9002

Die n.	MATERIAL 18 SNG AL ALLOY 1200-BS1470			DRAWING n.	
Factor	GENERAL TOLERANCES Extrusion UNI EN 755			437904	
Perim.	Machining UNI EN 22768			Vis. n.	
Area	FINISH BLACK ANODISE			Description:	
Weight	Note:			HTSK TV1500	
REF: ZA2565	Drawn E.De Nardo	Check A	11May06	ORIGINAL (was ZA2565-4)	Format A4
	REV	Date	Revision description		Scale 1:1
					1
					By