



# Customer Specification

## PART NO. 1299/37C

### Construction

				<b>Diameters (In)</b>	
1) Component 1		37 X 1 COND			
a) Conductor		22 (7/30) AWG TC			
b) Insulation		0.010" Wall, Nom. PVC		0.050	
(1) Color Code		Alpha Wire Company Color Code D			
Cond	Color	Cond	Color	Cond	Color
1	BLACK	14	RED/YELLOW	27	WHITE/BLACK/YELLOW
2	RED	15	RED/BLACK	28	WHITE/BLACK/BLUE
3	WHITE	16	WHITE/BLACK	29	WHITE/BLACK/BROWN
4	GREEN	17	WHITE/RED	30	WHITE/BLACK/ORANGE
5	ORANGE	18	WHITE/GREEN	31	WHITE/BLACK/SLATE
6	BLUE	19	WHITE/YELLOW	32	WHITE/BLACK/VIOLET
7	BROWN	20	WHITE/BLUE	33	WHITE/BLACK/BLACK
8	YELLOW	21	WHITE/BROWN	34	WHITE/RED/BLACK
9	VIOLET	22	WHITE/ORANGE	35	WHITE/RED/RED
10	SLATE	23	WHITE/SLATE	36	WHITE/RED/GREEN
11	PINK	24	WHITE/VIOLET	37	WHITE/RED/BLUE
12	TAN	25	WHITE/BLACK/RED		
13	RED/GREEN	26	WHITE/BLACK/GREEN		
2) Cable Assembly		37 Components Cabled			
a) Twists:		2.4 Twists/foot (min)			
3) Shield:		Alum/Mylar Tape, 25% Overlap, Min.			
a) Foil Direction		Foil Facing Out			
b) Drain Wire		22 (7/30) AWG TC			
4) Jacket		0.032" Wall, Nom.,PVC		0.418 (0.440 Max.)	
a) Color(s)		SLATE			
b) Print		ALPHA WIRE-* P/N 1299/37C 37C 22 AWG SHIELDED 75C (UL) TYPE CM OR AWM 2576 --- LLXXXXXX CSA TYPE CMG FT4 ROHS * = Factory Code <i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>			

## Applicable Specifications

1) UL	AWM/STYLE 2576	80&deg;C / 150 V <sub>RMS</sub>
	CM	75&deg;C
	VW-1	
2) CSA International	CMG	60&deg;C
	FT4	

## Environmental

1) EU Directive 2002/95/EC(RoHS):	
	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

## Properties

Physical & Mechanical Properties	
1) Temperature Range	-20 to 80&deg;C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	209 Lbs, Maximum
Electrical Properties (For Engineering purposes only)	
1) Voltage Rating	300 V <sub>RMS</sub>
2) Capacitance	50 pf/ft @ 1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	90 pf/ft @ 1 kHz, Nominal
4) Inductance	0.18 µH/ft, Nominal
5) Conductor DCR	16.5 O/1000ft @ 20&deg;C, Nominal
6) OA Shield DCR	10.4 O/1000ft @ 20&deg;C, Nominal

## Other

1) Packaging	
a) 1000 FT	
b) 500 FT	
c) 100 FT	

[www.alphawire.com](http://www.alphawire.com)

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

## RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:1299/37C

1299/37C , RoHS-Compliant Commencing With8/1/2005Production

*This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.***

<b>Substance</b>	<b>Maximum Control Value</b>
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.1% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) Including Deca-BDE	0.1% by weight (1000 ppm)

*The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.*

Authorized Signatory for the Alpha Wire Company:

Dave Watson, Director of Engineering &QA

1/20/2011