



NOTES:

1. Rating: 300V 8A (IEC 250V 10A)
PITCH: 5.00mm
2. Insulation Withstands Voltage:
AC 2000V/MIN
3. Insulation Resistance:
500M Ω or more at DC500V
4. Using Temperature Range:
-40°C~+105°C
5. Screw Torque Value: 4 kg-cm
6. Suitable Electric Wire: AWG 26~14
(0.5~1.5mm²)
7. Undimensioned Tolerances:

-	∧	□	0.05/10
⊥	//	≡	0.2/10
PITCH ERROR			0.05/10
UNDIMENSIONED TOLERANCES			±0.3

P	2	3	4	5	6	7	8	9	10	11	12	13	14
U	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
V	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00	70.00
P	15	16	17	18	19	20	21	22	23	24	25	26	
U	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	125.0	
V	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	125.0	130.0	

Tolerances For PITCH ERROR

4	SOLDER PIN	0082BD0100	P	BRASS	Tin Plated
3	CLAMP	0012BD0600	P	Stainless Steel	
2	SCREW	S000004800	P	STEEL	M2.5 Zn Plated
1	HOUSING	0082A0XX00	1	PA66(V2)	GREEN
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
DWG.		DATE	99,11,25	UNITS	MM SHEET/OF 1/2
CHK.		DATE		SCALE	3:1 (:)
APP.		DATE		NAME	20.590M/XX
				DWG NO.	

△		梁紅英	01.5.30
REV.	CONTENT	CHK.	DATE

