

# DL CONTACTS FOR ZERO INSERTION FORCE CONNECTORS


Order Code 152-052 TO 152-055

Farnell Technical Data Service

The DL 'centre carrier contacts are being phased out in favour of 'T carrier' contacts.

### CENTRE CARRIER

- o "Donut" style carrier strip goes through centre of contact.
- o 3 contacts covering 18-28 Awg.
- o Rough edges on loose pieces.
- o "Donuts" foul up semi-automatic crimping equipment.



#### T-CARRIER

- o T-carrier strip runs along tip of contact.
- o No rough edges no foul up of semiautomatic crimping equipment.
- o 2 contacts covering 24-32 Awg equates to a better, tighter crimp.



# OLD FEC ORDER CODES - CENTRE CARRIER

CABLE SIZE	CONTACT	SUITABLE CRIMP TOOL
24 to 28 Awg	140-980 (030-2064-010	140-982 (CCT-DL)

#### REPLACEMENT FEC ORDER CODES - T CARRIER

CABLES SIZE	CONTACT	SUITABLE CRIMP TOOL
24 to 26 Awg	152-052 (030-2410-001)	152-054 (CCT-DLT)
28 to 32 Awg	152-053 (030-2416-001)	152-055 (CCT-DLT1)

NOTE: - Centre carrier 24 - 28 Awg replaced by two T carrier contacts.

Numbers in brackets are manufacturers part numbers.



APPLICATION AND MAINTENANCE FOR CANNON HAND CRIMP TOOLS NO'S CCT-DLT, 995-0002-154 CCT-DLT-1, 995-0002-084

995-0001-903

INSTRUCTION SHEET

NO. 370-0017-000

Released MAY, 1990

## INTRODUCTION

These tools are designed to crimp the "DL" series contacts listed in Figure 5. All three tools feature a contact locator, positive crimp height stop and a full cycle ratchet release mechanism. See Section I for proper use of these tools.

CCT-DL-3.




FIGURE 1

## Section I Application

- 1. Strip wire to length specified in Figure 5.
- 2. Place contact in appropriate locator nest as indicated by wire size.
- 3. Partially close tool (one of two clicks) to hold contact. Insert wire into contact until it touches stop (See Figure 2). While holding wire in place close tool completely until ratchet releases. Open handles and remove contact.

#### NOTE:

In emergency, the tool can be opened prematurely by releasing the ratchet pawl with a small screwdriver (See Figure 3).




FIGURE 2




FIGURE 3

### Section II - Maintenance

- Periodically clean the crimp jaws with a brush or cotton swab and inspect for excessive wear or damage.
- 2. Check that ratchet is functioning properly.
- 3. Apply a drop of light weight oil to all pivot points.
- 4. Check that locator is free to slide.

# Section III - Quality Control

- 1. Check that stripping process is not cutting any wire strands.
- 2. Check that wire is properly positioned in contact (See Figure 4).
- 3. Check contact straightness after crimping.

  Maximum allowable bend is 2° in any direction.
- 4. Randomly check integrity of crimp by measuring wire retention force. Place the contact in an appropriate holding fixture and pull on wire with a tensile force gauge until the wire breaks or separates from contact. Measured force must meet or exceed the minimum tensile values listed in Figure 5.




FIGURE 4

Tool/Part Number	Contact Number		Wire Strip		Min. Tensile
	Loose	Reel	Length (Ins.)	AWG	(Lbs.)
CCT-DL-3 995-0001-903	030-2415-001	110238-0402	.160	18	30
	030-2415-003	110238-0481			
	030-2493-001	110238-0485		20	19
<u>CCT-DLT</u> 995-0002-154	030-2409-001	110238-0400	.130	20	19
	030-2409-003	110238-0479		20	13
	030-2491-001	110238-0483		22	12
	030-2410-001	110238-0401	.130	24	8
	030-2410-003	110238-0480			
	030-2492-001	110238-0484		26	5
CCT-DLT-1 995-0002-084	030-2416-001	110238-0403	.130	28	3
	030-2416-003	110238-0482		30	1.5
	030-2494-001	110238-0486		32	1

FIGURE 5