

# Customer Information Sheet

DRAWING No.: M22-30500XX

SHEET 2 OF 2







IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



## NOTES:

1. TO BE USED WITH CRIMP MOULDINGS M22-301XX00 OR M22-302XX00.
2. FOR HAND CRIMPING ONTO WIRE, USE HAND TOOL Z22-020 (INSTRUCTION SHEET IS-05). STRIP WIRE BY 1.0mm MAX BEFORE CRIMPING
3. SUITABLE FOR WIRE GAUGES 24-30 AWG.
4. CONTACTS SUPPLIED LOOSE IN QUANTITIES OF 100.
5. ALL TOLERANCES ARE  $\pm 0.20$  UNLESS OTHERWISE STATED.

ORDER CODE:

**M22-30500XX**

FINISH:

- 06 - TIN/LEAD
- 22 - SELECTIVE GOLD + TIN/LEAD
- 42 - SELECTIVE GOLD + 100% TIN
- 46 - 100% TIN

JMB 4 28.10.05 8813

NAME ISS. DATE C/NOTE

APPROVED:

CHECKED:

DRAWN: A. LIOTTA

CUSTOMER REF.:

ASSEMBLY DRG:

# HARWIN

HARWIN USA  
TEL: 603 893 5376  
FAX: 603 893 5396  
mjs@harwin.com

HARWIN Europe (UK)  
TEL: 023 9231 4545  
FAX: 023 9231 4590  
mjs@harwin.co.uk

HARWIN Asia  
TEL: +65 6 779 4909  
FAX: +65 6 779 3868  
mjs@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

## TOLERANCES

X. =  $\pm 1mm$   
X.X =  $\pm 0.25mm$   
X.XX =  $\pm 0.10mm$   
X.XXX =  $\pm 0.01mm$   
ANGLES =  $\pm 5^\circ$   
UNLESS STATED

MATERIAL:

PHOSPHOR BRONZE

FINISH: SEE ORDER CODE

S/AREA: mm<sup>2</sup>

TITLE:

CRIMP CONTACT (LOOSE)

DRAWING NUMBER:

**M22-30500XX**

SHT  
2  
OF  
2