

V RANGE



FEATURES

- Wall or window mounting
- Single speed thermal overload protected motor
- Moulded in white and dove grey ABS plastic
- Integral electrical connector/isolator

TERMINOLOGY

A	Complete with time delay automatic shutters
R	Reversible motor (intake/extract)
I	Flush fitting/recessed. Wall mount only
M	Manual operation complete with pull cord operated shutters

MODELS

Type	Code	Farnell code	Specification
V23/9ARI	12750	7003067	Extract capacity 620 m ³ /hr (172.2 l/s). Intake capacity 420 m ³ /hr (116.7 l/s). Watts 37. dBA @ 3m 50 370mm high x 355mm wide x 13.5mm deep (when fitted)
V30/12ARI	12740	7003079	Extract capacity 1125m ³ /hr (312.5 l/s). Intake capacity 750 m ³ /hr (208.3 l/s). Watts 74. dBA @ 3m 56 370mm high x 355mm wide x 13.5mm deep (when fitted)

ACCESSORIES

Type	Code	Farnell code	Specification
VWR	13070	7005593	Set of 4 wall rods and nuts for Vortice Range