Environment						
Conforming to standards			IEC/EN 60947-4-1, NF C 63-650, VDE 0660			
Approvals	Pending		UL, CSA			
Protective treatment	Conforming to IEC 68 (DIN 50016)		"TC" (Klimafest, Climateproof)			
Degree of protection	Conforming to VDE 0106		Protection against direct finger contact			
Ambient air temperature	Storage	°C	- 40+ 70			
around the device	For normal operation (IEC 947)	°C	- 20+ 55 (without derating)			
	Operating limit	°C	- 30+ 60 (with derating) (1)			
Maximum operating altitude	Without derating	m	2000			
Operating positions	Vertical axis		Horizontal axis			
	90° — 90° — Without derating		90° With derating (1)			
Flame resistance	Conforming to UL 94 Conforming to NF F 16-101 and 16-102		Self-extinguishing material V1			
Shock resistance, hot state (1/2 sine wave, 11 ms)	Conforming to IEC 68, N/C contact Conforming to IEC 68, N/O contact		Conforming to requirement 2 10 gn 10 an			
Vibration resistance, hot state 5 to 300 Hz	Conforming to IEC 68, N/C contact Conforming to IEC 68, N/O contact		2 gn 2 gn			
Safe separation of circuits	Conforming to VDE 0106 and IEC 536		VLSV (2), up to 400 V			
Cabling Screw clamp terminals	Solid cable Flexible cable without cable end Flexible cable with cable end	mm²	Minimum Maximum Maximum to IEC 94 1 x 1.5 2 x 4 1 x 4 + 1 x 2.5 1 x 0.75 2 x 4 2 x 2.5 1 x 0.34 1 x 1.5 + 1 x 2.5 1 x 1.5 + 1 x 2.5			
Tightening torque	Philips head n° 2 - Ø 6		0.8			
Mounting	Trimps nead in 2 900	IX.III	Directly under the contactor or reversing contactor			
Connections	Made automatically when mounted under the - contactor terminal A2 connected to overload - contactor terminal 14 connected to overload When using 3 P + N/C, or 4 P contactors, or t voltage, break off the link marked 14. (1) Please call our Customer information centres.	I relay termina I relay terminal he N/O auxilia	follows: il 96 on all products, il 95 on products with 3 P + N/O. rry contact marked 13-14, at a voltage other than the co			
	(2) Very low safety voltage.					


Auxiliary contact characteristics									
Number of contacts			1 N/C	C + 1 N	I/O				
Conventional thermal current		Α	6						
Short-circuit protection	Conforming to IEC 947, VDE 0660. gG fuse or circuit-breaker GB2-CB●●	A	6 ma	x.					
Maximum power of the controlled contactor coils (sealed) (Occasional operating cycles of contact 95-96)	a.c.	V VA	24 100	48	110 400	220/230	400 600	415/440 600	600/690
	d.c.	V	24	48	110	220		_	_
		w	100	100	50	45	35	_	_
Maximum operational voltage	a.c., category AC-15	v	690						
	d.c., category DC-13	v	250						

Dimensions: page 2/47 References: page 2/46 Schemes: page 2/47


Electrical characteristics of	the power circuit		
Rated operational voltage (Ue)	Up to	v	690
Rated insulation voltage (Ui)	Conforming to IEC/EN 60947-4-1 Conforming to VDE 0110 group C Conforming to CSA C 22-2 n° 14	V V	690 750 600
Rated impulse withstand voltage (Uimp)	Conforming to CSA C 22-2 II 14	kV	6
Frequency limits of the operational current		Hz	Up to 400
Power dissipated per pole		w	2
Operating characteristics			
Sensitivity to phase failure	Conforming to IEC 947		Yes
Reset	Manual or automatic		Selected by means of a lockable and sealable switch on the front of the relay
Signalling	On front of relay		Trip indicator
Reset-Stop function			Pressing the Reset-Stop button: - actuates the N/C contact - has no effect on the N/O contact
Test function	By pushbutton		Pressing the Test button enables: - checking of the control circuit wiring - simulation of overload tripping (actuation of both N/C and N/O contacts, and of the trip indicator)
Short-circuit protection			See page 2/46

Tripping curves

Average operating time related to multiples of the current setting Class 10 A



Balanced 3-phase operation, from cold state



Balanced operation with 2 phases only, from cold state

- 1 Setting: at lower end of scale
- 2 Setting: at upper end of scale

References:	Dimensions:	Schemes:
page 2/46	page 2/47	page 2/47

3-pole relays with screw clamp terminals

These overload relays are designed for the protection of motors. They are compensated and phase failure sensitive. Resetting can either be manual or automatic.

Direct mounting: under the contactor for versions with screw clamp terminals only; pre-wired terminals, see pages 2/44 and 2/47.

Separate mounting: using terminal block LA7-K0064 (see below).

- On the front face of the overload relay:
 selection of reset mode: Manual (marked H) or Automatic (marked A),
- red pushbutton: Trip Test function,

blue pushbutton: Stop and manual Reset,
yellow trip flag indicator: overload relay tripped.
Protection by fuses or by magnetic circuit-breaker type GV2-LE, see page 3/41

Relay setting range		be used v m rating	vith selected relay	Reference	Weight
90	aM	gG	BS88		
Α	Α	Ā	Α		kg
Class 10 A (t	he standard	l specifies a	a tripping time of between 2	and 10 seconds at 7.2 ln)	
0.110.16	0.25	2	2	LR2-K0301	0.145
0.160.23	0.25	2	2	LR2-K0302	0.145
0.230.36	0.5	2	2	LR2-K0303	0.145
0.360.54	1	4	4	LR2-K0304	0.145
0.540.8	1	4	4	LR2-K0305	0.145
0.81.2	2	6	6	LR2-K0306	0.145
1.21.8	2	6	6	LR2-K0307	0.145
1.82.6	4	10	10	LR2-K0308	0.145
2.63.7	4	16	16	LR2-K0310	0.145
3.75.5	6	16	16	LR2-K0312	0.145
5.58	8	20	20	LR2-K0314	0.145
811.5	10	25	20	LR2-K0316	0.145
1014	16	32	25	LR2-K0321	0.145
1216	20	40	32	LR2-K0322	0.145



LR2-K0301



LA7-K0064

Overload relays for unbalanced loads

Class 10 A: To order, replace the prefix LR2 by LR7 in the references selected from above (only applicable to overload relays LR2-K0305 to LR2-K0322). Example: LR7-K0308.

Accessory			
Description	Type of connection	Reference	Weight kg
Terminal block for separate clip-on mounting of the overload relay on 35 mm rail	Screw clamp	LA7-K0064	0.100

Characteristics: pages 2/44 and 2/45


Dimensions: page 2/47


Schemes: page 2/47

2.2


LR2-K


Direct mounting beneath the contactor





Separate mounting with terminal block LA7-K0064 on 35 mm -- rail (AM1-DP200 or AM1-DE200)







AM1-	С	
DP200	78.5	
DE200	86	

LR2-K


Test Reset/stop







Note: If pre-wiring is not required, break off the 2 links located on the thermal overload relay.



Characteristics: pages 2/44 and 2/45

References: page 2/46