
# Quad MECL to TTL Translator

The MC10125 is a quad translator for interfacing data and control signals between the MECL section and saturated logic sections of digital systems. The MC10125 incorporates differential inputs and Schottky TTL "totem pole" outputs. Differential inputs allow for use as an inverting/ non-inverting translator or as a differential line receiver. The VBB reference voltage is available on pin 1 for use in single-ended input biasing. The outputs of the MC10125 go to a low logic level whenever the inputs are left floating.

Power supply requirements are ground,  $\pm 5.0$  Volts and  $\pm 5.2$  Volts. Propagation delay of the MC10125 is typically 4.5 ns. The MC10125 has fanout of 10 TTL loads. The dc levels are MECL 10,000 in and Schottky TTL, or TTL out. This device has an input common mode noise rejection of  $\pm 1.0$  Volt.

An advantage of this device is that MECL level information can be received, via balanced twisted pair lines, in the TTL equipment. This isolates the MECL logic from the noisy TTL environment. This device is useful in computers, instrumentation, peripheral controllers, test equipment and digital communications systems.


- $P_D = 380 \text{ mW typ/pkg (No Load)}$
- $t_{pd} = 4.5 \text{ ns typ } (50\% \text{ to} + 1.5 \text{ Vdc out})$
- $t_r$ ,  $t_f = 2.5$  ns typ (1.0 V to 2.0 V)



 $^*V_{BB}$  to be used to supply bias to the MC10125 only and bypassed (when used) with 0.01  $\mu F$  to 0.1  $\mu F$  capacitor to ground (0 V).  $V_{BB}$  can source < 1.0 mA.

When the input pin with the bubble goes positive, the output goes negative.

# DIP PIN ASSIGNMENT



Pin assignment is for Dual–in–Line Package.
For PLCC pin assignment, see the Pin Conversion Tables on page 18 of the ON Semiconductor MECL Data Book (DL122/D).



## ON Semiconductor

http://onsemi.com

#### MARKING DIAGRAMS



CDIP-16 L SUFFIX CASE 620 MC10125L AWLYYWW



PDIP-16 P SUFFIX CASE 648





PLCC-20 FN SUFFIX CASE 775



A = Assembly Location

WL = Wafer Lot YY = Year

WW = Work Week

#### ORDERING INFORMATION

Device	Package	Shipping
MC10125L	CDIP-16	25 Units / Rail
MC10125P	PDIP-16	25 Units / Rail
MC10125FN	PLCC-20	46 Units / Rail

# **ELECTRICAL CHARACTERISTICS**

			Test Limits							
		Pin Under	–30°C		+25°C			+85°C		]
Characteristic	Symbol	Test	Min	Max	Min	Тур	Max	Min	Max	Unit
Negative Power Supply Drain Current	ΙE	8		-44			-40		-44	mAdc
Positive Power Supply	ICCH	9		52			52		52	mAdc
Drain Current	ICCL	9		39			39		39	mAdc
Input Current	l <sub>inH</sub> 1	2		180			115		115	μAdc
Input Leakage Current	ICBO	2		1.5			1.0		1.0	μAdc
High Output Voltage	Voн	4	2.5		2.5			2.5		Vdc
Low Output Voltage	VOL	4		0.5			0.5		0.5	Vdc
High Threshold Voltage	VOHA	4	2.5		2.5			2.5		Vdc
Low Threshold Voltage	VOLA	4		0.5			0.5		0.5	Vdc
Indeterminate Input	V <sub>OLS1</sub>	4		0.5			0.5		0.5	Vdc
Protection Tests	V <sub>OLS2</sub>	4		0.5			0.5		0.5	Vdc
Short Circuit Current	los	4	40	100	40		100	40	100	mAdc
Reference Voltage	V <sub>BB</sub>	1	-1.420	-1.280	-1.350		-1.230	-1.295	-1.150	Vdc
Common Mode Rejection Tests	Voн	4 4	2.5 2.5		2.5 2.5			2.5 2.5		Vdc
	V <sub>OL</sub>	4 4		0.5 0.5			0.5 0.5		0.5 0.5	Vdc
Switching Times (50 $\Omega$ Load)										ns
Propagation Delay (50% to +1.5Vdc)	<sup>t</sup> 6+5- <sup>t</sup> 6-5+ <sup>t</sup> 2+4- <sup>t</sup> 2-4+	5 5 4 4	1.0 1.0 1.0 1.0	6.0 6.0 6.0 6.0	1.0 1.0 1.0 1.0	4.5 4.5 4.5 4.5	6.0 6.0 6.0 6.0	1.0 1.0 1.0 1.0	6.0 6.0 6.0 6.0	
Rise Time (+1.0V to 2.0V) Fall Time (+1.0V to 2.0V)	t <sub>4+</sub> t <sub>4-</sub>	4 4		3.3 3.3			3.3 3.3		3.3 3.3	

Individually test each output, apply V<sub>IHmax</sub> to pin under test.

# **ELECTRICAL CHARACTERISTICS** (continued)

			TEST VOLTAGE VALUES (Volts)							
(	Test Temp	perature	V <sub>IHmax</sub>	V <sub>ILmin</sub>	V <sub>IHAmin</sub>	V <sub>ILAmax</sub>	VIHH	VILH		
		-30°C	-0.890	-1.890	-1.205	-1.500	+0.110	-0.890		
		+25°C	-0.810	-1.850	-1.105	-1.475	+0.190	-0.850		
		+85°C	-0.700	-1.825	-1.035	-1.440	+0.300	-0.825		
		Pin	TEST	VOLTAGE A	APPLIED TO	PINS LIST	ED BELC	)W		
Characteristic	Symbol	Under Test	V <sub>IHmax</sub>	V <sub>ILmin</sub>	VIHAmin	V <sub>ILAmax</sub>	V <sub>IHH</sub>	VILH	Gnd	Output Condition
Negative Power Supply Drain Current	lΕ	8							16	
Positive Power Supply	ICCH	9	2,6,10,14						16	
Drain Current	ICCL	9		2,6,10,14					16	
Input Current	linH1	2	2,6,10,14						16	
Input Leakage Current	ICBO	2							16	
High Output Voltage	VOH	4		2,6,10,14					16	–2.0mA
Low Output Voltage	VOL	4	2,6,10,14						16	20mA
High Threshold Voltage	VOHA	4		6,10,14		2			16	-2.0mA
Low Threshold Voltage	VOLA	4	6,10,14		2				16	20mA
Indeterminate Input	V <sub>OLS1</sub>	4							16	20mA
Protection Tests	V <sub>OLS2</sub>	4							16	20mA
Short Circuit Current	los	4		2,6,10,14					4, 16	
Reference Voltage	V <sub>BB</sub>	1		2,6,10,14						
Common Mode Rejection Tests	VOH	4 4					3	2	16 16	–2.0mA –2.0mA
	VOL	4 4					2	3	16 16	20mA 20mA
Switching Times (50 $\Omega$ Load)			Pulse In	Pulse Out	C <sub>L</sub> (pF)					
Propagation Delay (50% to +1.5Vdc)	t <sub>6+5</sub> - t <sub>6-5+</sub> t <sub>2+4-</sub> t <sub>2-4+</sub>	5 5 4 4	6 6 2 2	5 5 4 4	25 25 25 25 25				16 16 16 16	
Rise Time(+1.0V to 2.0V)	t <sub>4+</sub>	4	2	4	25				16	
Fall Time (+1.0V to 2.0V)	t <sub>4</sub> _	4	2	4	25				16	

Individually test each output, apply V<sub>IHmax</sub> to pin under test.


# **ELECTRICAL CHARACTERISTICS** (continued)

			TEST VOLTAGE VALUES (Volts)						
0	Test Temp	erature	VIHH	VILH	V <sub>BB</sub>	VCC	VEE	1	
–30°C		-1.890	-2.890	From +5.0		-5.2	1		
		+25°C	-1.810	-2.850	Pin	+5.0	-5.2	1	
		+85°C	-1.700	-2.825	1	+5.0	-5.2	]	
		Pin	TEST	VOLTAG	E APPLIED TO	PINS LISTE	D BELOW	]	
Characteristic	Symbol	Under Test	V <sub>IHH</sub>	V <sub>ILH</sub>	V <sub>BB</sub>	v <sub>cc</sub>	V <sub>EE</sub>	Gnd	Output Condition
Negative Power Supply Drain Current	Ē	8			3,7,11,15	9	8	16	
Positive Power Supply	ICCH	9			3,7,11,15	9	8	16	
Drain Current	ICCL	9			3,7,11,15	9	8	16	
Input Current	l <sub>inH</sub> 1	2			3,7,11,15	9	8	16	
Input Leakage Current	ICBO	2			3,7,11,15	9	2,6,8,10,14	16	
High Output Voltage	Vон	4			3,7,11,15	9	8	16	-2.0mA
Low Output Voltage	VOL	4			3,7,11,15	9	8	16	20mA
High Threshold Voltage	Vона	4			3,7,11,15	9	8	16	-2.0mA
Low Threshold Voltage	VOLA	4			3,7,11,15	9	8	16	20mA
Indeterminate Input Protection Tests	VOLS1	4				9	2,3,6,7,8, 10,11,14,15	16	20mA
	V <sub>OLS2</sub>	4				9	8	16	20mA
Short Circuit Current	los	4			3,7,11,15	9	8	4, 16	
Reference Voltage	V <sub>BB</sub>	1			3,7,11,15				
Common Mode Rejection Tests	Voн	4 4	3	2		9 9	8 8	16 16	–2.0mA –2.0mA
	V <sub>OL</sub>	4 4	2	3		9 9	8 8	16 16	20mA 20mA
Switching Times (50Ω Load)									
Propagation Delay (50% to +1.5Vdc)	t <sub>6+5</sub> t <sub>6-5+</sub> t <sub>2+4-</sub> t <sub>2-4+</sub>	5 5 4 4			3,7,11,15 3,7,11,15 3,7,11,15 3,7,11,15	9 9 9 9	8 8 8 8	16 16 16 16	
Rise Time (+1.0V to 2.0V)	t <sub>4+</sub>	4			3,7,11,15	9	8	16	
Fall Time (+1.0V to 2.0V)	t <sub>4</sub> _	4			3,7,11,15	9	8	16	

<sup>1.</sup> Individually test each output, apply V<sub>IHmax</sub> to pin under test.


Each MECL 10,000 series circuit has been designed to meet the dc specifications shown in the test table, after thermal equilibrium has been established. The circuit is in a test socket or mounted on a printed circuit board and transverse air flow greater than 500 linear fpm is maintained. Outputs are terminated through a 50-ohm resistor to –2.0 volts. Test procedures are shown for only one gate. The other gates are tested in the same manner.

# **SWITCHING TIME TEST CIRCUIT**



#### PACKAGE DIMENSIONS

#### PLCC-20 **FN SUFFIX** PLASTIC PLCC PACKAGE CASE 775-02 **ISSUE C**



⊕ 0.010 (0.250)⑤ T L-M ⑤ N ⑥

- WHERE TOP OF LEAD SHOULDER EXITS PLASTIC BODY AT MOLD PARTING LINE.
- 2. DIMENSION G1, TRUE POSITION TO BE MEASURED AT DATUM -T-, SEATING PLANE.


  3. DIMENSIONS R AND U DO NOT INCLUDE MOLD.
- FLASH. ALLOWABLE MOLD FLASH IS 0.010 (0.250) PER SIDE.

  4. DIMENSIONING AND TOLERANCING PER ANSI
- 4. DIMENSIONING AND TOLERANCING FER ANSI Y14.5M, 1982. 5. CONTROLLING DIMENSION: INCH. 6. THE PACKAGE TOP MAY BE SMALLER THAN THE
- PACKAGE BOTTOM BY UP TO 0.012 (0.300).
  DIMENSIONS R AND U ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY EXCLUSIVE OF MOLD FLASH, TIE BAR BURRS, GATE BURRS AND INTERLEAD FLASH, BUT INCLUDING ANY MISMATCH BETWEEN THE TOP
- INCLUDING ANY MISMAICH BE I WEEN THE TOP AND BOTTOM OF THE PLASTIC BODY.

  7. DIMENSION H DOES NOT INCLUDE DAMBAR PROTRUSION OR INTRUSION. THE DAMBAR PROTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE GREATER THAN 0.037 (0.940). THE DAMBAR INTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE SMALLER THAN 0.025 (0.635).


	INC	HES	MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.385	0.395	9.78	10.03
В	0.385	0.395	9.78	10.03
С	0.165	0.180	4.20	4.57
Ε	0.090	0.110	2.29	2.79
F	0.013	0.019	0.33	0.48
G	0.050	BSC	1.27	BSC
Н	0.026	0.032	0.66	0.81
J	0.020		0.51	
K	0.025		0.64	
R	0.350	0.356	8.89	9.04
U	0.350	0.356	8.89	9.04
٧	0.042	0.048	1.07	1.21
W	0.042	0.048	1.07	1.21
Х	0.042	0.056	1.07	1.42
Υ		0.020		0.50
Z	2°	10°	2 °	10°
G1	0.310	0.330	7.88	8.38
K1	0.040		1.02	


## **PACKAGE DIMENSIONS**



- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.
  3. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
  4. DIMENSION F MAY NARROW TO 0.76 (0.030) WHERE THE LEAD ENTERS THE CERAMIC BODY.

	INC	HES	MILLIMETERS		
DIM	MIN MAX		MIN	MAX	
Α	0.750	0.785	19.05	19.93	
В	0.240	0.295	6.10	7.49	
С		0.200		5.08	
D	0.015	0.020	0.39	0.50	
Ε	0.050	BSC	1.27 BSC		
F	0.055	0.065	1.40	1.65	
G	0.100	BSC	2.54 BSC		
Н	0.008	0.015	0.21	0.38	
K	0.125	0.170	3.18	4.31	
L	0.300	BSC	7.62 BSC		
M	0°	15°	0 °	15°	
N	0.020	0.040	0.51	1.01	





- NOTES:

  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

  2. CONTROLLING DIMENSION: INCH.

  3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.

  4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.

  5. ROUNDED CORNERS OPTIONAL.

	INC	HES	MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.740	0.770	18.80	19.55	
В	0.250	0.270	6.35	6.85	
С	0.145	0.175	3.69	4.44	
D	0.015	0.021	0.39	0.53	
F	0.040	0.70	1.02	1.77	
G	0.100	BSC	2.54 BSC		
Н	0.050	BSC	1.27 BSC		
J	0.008	0.015	0.21	0.38	
K	0.110	0.130	2.80	3.30	
L	0.295	0.305	7.50	7.74	
M	0°	10 °	0 °	10 °	
S	0.020	0.040	0.51	1.01	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

#### PUBLICATION ORDERING INFORMATION

North America Literature Fulfillment:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA **Phone**: 303–675–2175 or 800–344–3860 Toll Free USA/Canada **Fax**: 303–675–2176 or 800–344–3867 Toll Free USA/Canada

Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

EUROPE: LDC for ON Semiconductor - European Support

**German Phone:** (+1) 303–308–7140 (M–F 2:30pm to 5:00pm Munich Time)

Email: ONlit-german@hibbertco.com

French Phone: (+1) 303–308–7141 (M–F 2:30pm to 5:00pm Toulouse Time)

Email: ONlit-french@hibbertco.com

English Phone: (+1) 303–308–7142 (M–F 1:30pm to 5:00pm UK Time)

Email: ONlit@hibbertco.com

ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303–675–2121 (Tue–Fri 9:00am to 1:00pm, Hong Kong Time) Toll Free from Hong Kong 800–4422–3781

Email: ONlit-asia@hibbertco.com

**JAPAN**: ON Semiconductor, Japan Customer Focus Center 4–32–1 Nishi–Gotanda, Shinagawa–ku, Tokyo, Japan 141–8549

**Phone**: 81–3–5740–2745 **Email**: r14525@onsemi.com

Fax Response Line: 303-675-2167

800-344-3810 Toll Free USA/Canada

ON Semiconductor Website: http://onsemi.com

For additional information, please contact your local

Sales Representative.