




## Engineering Data


**C**  
**Alkaline 1.5V**  
 No Added Mercury or Cadmium

### ENERGIZER NO. E93



Millimeters	Inches
0.50	0.020
1.50	0.059
7.50	0.295
13.31	0.524
13.47	0.530
24.90	0.980
26.20	1.031
46.10	1.815
46.60	1.835
48.50	1.909
50.00	1.969

NEGATIVE COVER VIEW



**Chemical System:** Zinc-Manganese Dioxide (Zn/MnO<sub>2</sub>)

**Designation:** ANSI-14A, IEC-LR14

**Battery Voltage:** 1.5 Volts

**Average Weight:** 66.2 grams (2.3 oz.)

**Volume:** 26.9 cubic centimeters (1.6 cubic inch)

**Average Service capacity (to 0.8 Volts / cell):** 8350 mAh


(Rated Capacity at 25 mA continuous drain)

**Cell:** One No. 3-335 (size "C")


**Jacket:** Plastic Label

**Shelf Life:** 7 years


### Temperature Effects Typical Service to 0.8 Volts




### Constant Resistance Discharge Typical Service







### Constant Current Discharge Typical Service



**ENERGIZER NO. E93**



**Typical Applications**



**Important Notice**

This data sheet contains information specific to batteries manufactured at time of its publication. Please contact your Energizer representative for most current information. Contents herein do not constitute a warranty.