

3-348-802-03 12/6.07

- Clear-cut operating menus
- Illuminated display
- Two 4 m measurement cables (4-wire connection)
- · Remote control for efficient use
- Limit value adjustment
- Convenient memory and report generating functions
- Data interfaces for PC and printer
- Can be expanded for quick, on-site alphanumeric data entry and reports printing
- Can be retrofitted for high-voltage testing



Applications

The PROFITEST 204 tester has been designed for quick, safe testing of electrical and electronic equipment and systems at machinery in accordance with DIN EN 60204-1 and VDE 0113 with nominal voltages of up to 1000 V.

The following periodic tests must be performed in accordance with the standard:

- Testing for continuity at connections within the protective conductor system with 10 A test current
- Insulation resistance test
- Voltage tests (optionally HP or HV)
- Testing for residual voltage

Beyond this, the following tests and measurements may be performed as well:

- Leakage current test
- Voltage measurement
- Frequency measurement

All values required for approval reports can be measured with this instrument.

Display

The LCD window consists of an illuminated dot matrix display at which menus, device settings and measurement results, as well as online help can be displayed.

Help Key

Information regarding the current menu item can be queried with this key. Online help texts appears at the LCD window.

Function Selector Switch

Testing, report generating and data management functions are selected with the rotary switch.

Limit Values

Limit values can be assigned for use with each measurement, allowing for individualized adaptation of the various tests to prevailing local conditions, as well as to the latest requirements set forth in the standards.

Data Memory

Depending upon the number of systems for which data logging is performed (max. 254), up to 2800 measurements can be saved to memory.

Remote Control

The test probe with integrated control panel allows for remote control of protective conductor and insulation resistance measurements, as well as storage of the respective values to memory. Integrated lamps indicate measurement progress status. All PROFITEST 204 operating functions can also be controlled via the RS 232 interface. Signal and display values can be remote queried as well.

RS 232 Interface for Input Module and PC

This port provides for data transmission and the supply of electrical power to the optionally available **SECUTEST** | **SI** input module.

Other devices (e.g. a PC) can also be connected to this port with the help of an interface cable.

CENTRONICS Parallel Port

Any commercially available printer can be connected to this data interface (except for PostScript printers). Detailed report forms which have been uploaded to the instrument can be read out via this port.

Report Generating Functions

The following report generating functions are available:

- Upload report forms to the test instrument with the help of a PC and included PROTOCOL software
- Select one of three report forms stored to the instrument
- Read out measurement data via the CENTRONICS parallel port to commercially available printers
- Transmit measurement data to a PC and process with EXCEL

Characteristic Values

| Meas. Quantity | 3 | | Resolu- Nom. Voltage | Open- | Nom. | Short- | Int. | Meas. Error | Intrinsic Error | Overload | | |
|--|----------------------------|---------------------|--------------------------------------|------------------------|------------------------------|---------------------|----------------|-------------|--|--|--------------------------------------|-------|
| | | tion U _N | Circuit Voltage U ₀ | I _N C | | | | | Capac- ity | Dura- tion | | |
| Protective Conductor | 0 85 mΩ 85 999 mΩ | 10 330 mΩ | 100 μΩ 1 mΩ | | 12 V ∼ | 10 A ¹⁾ | 12 A | | 1/0 C0/ rda . C d/ | ±(3% rdg. + 5 d) | Fuse: | |
| Resistance R _{SL} | 1.00 9.99 Ω 10.0 25.0 Ω | _ | 10 mΩ 100 mΩ | | 12 V ~ | _ | _ | | ±(8.6% rdg.+6 d) | ±(3% rdg. + 10 d) | 16 A/1000 V Breaking Capacity: | |
| Δ U ²⁾ | 0 9.99 V* | | 0.01 V | | 12 V ∼ | 10 A | 12 A | | | ±(2% rdg. + 3 d) | | kA |
| Δυ - ′ | 10.0 12.0 V | _ | 0.1 V | | 12 V ∼ | _ | _ | _ | _ | ±(10% rdg. + 3 d) | / | |
| | | 1 | | 1 | | | | | 1 | 1 | | |
| Insulation Resistance R _{ISO} | 0 999 kΩ 1.00 9.99 MΩ | 0.050 50 MΩ | | 100/250/500/ 1000 V | | J _N 1 mA | max. 1.6 mA | | $\pm (5.5\% \text{ rdg.} + 4 \text{ d})$ of $0.05\text{M}\Omega50\text{M}\Omega$ | ±(3% rdg. +2 d) | | |
| | 10.0 99.9 MΩ 100 499 MΩ | | 100 kΩ 1 MΩ | 250 V 500/1000 V | max. 1.3 • U _N | | | | _ | ±(8 % rdg. +2 d) ±(5 % rdg. +2 d) | 1200 V | cont. |
| | 500 999 MΩ 1 3 GΩ | | 1 MΩ 10 MΩ | 500/1000 V | | | | | | $\pm (10\% \text{ rdg.} + 2 \text{ d})$ $\pm (20\% \text{ rdg.} + 2 \text{ d})$ | | |
| | | | | | | | | | | (1 1 1 3 1) | | |
| Leakage Current ∆I | 0.00 9.99 mA | 0.2 9.9 mA | 0.01 mA | _ | _ | _ | _ | 2 kΩ | ±(8.6% rdg. +9 d) | ±(5% rdg. + 5 d) | 250 V | cont. |
| | | | | | | | | | | | | |
| Voltage U DC/AC | 0.0 99.9 V 100 999 V | 1.0 1000 V | 0.1 V 1 V | _ | _ | _ | _ | 20ΜΩ | ±(8.6% rdg. +9 d) | ±(5% rdg. + 5 d) | 1200 V | cont. |
| | 1.00 1.2 kV | | 0.01 kV | | | | | | | | | |
| Frequency | 8.099.9 Hz | 10 1000 15 | 0.1 Hz | | | | | 20140 | 1/0 60/ rdg 1 0 d\ | 1/20/ rda 1 1 d\ | 1200 V | oort |
| f~ | 100 999 Hz | 10 1000 HZ | 10 1000 Hz 1 Hz | | | | | | ±(8.6% rdg. +2 d) | $\pm (2\% \text{ rdg.} + 1 \text{ d})$ | 1200 V | cont. |

¹⁾ up to 330 m Ω maximum

²⁾ related to 10 A nominal current

Applicable Regulations and Standards

| IEC 204-1 DIN EN 60204-1 VDE 0113 Part 1 | Machine safety: Electrical equipment at machinery Part 1: General requirements |
|--|--|
| IEC 61010-1 DIN EN 61010-1 VDE 0411 Part 1 | Safety requirements for electrical equipment for measurement, control and laboratory use — General requirements |
| DIN EN 60529 DIN VDE 0470–1 | Protection provided by enclosures (IP code) |
| VDI/VDE 3540 | Reliability of measuring, control and regulating devices — Climatic categories for devices and accessories |
| DIN 43 751 Part 1, 2 | Digital measuring instruments |
| DIN EN 61326 VDE 0843 Part 20 | Electrical equipment for measurement, control and laboratory use – EMC requirements |

Regulations and Standards for Use of the Tester

| IEC 204–1 | Machine safety: | | | | |
|---|--|--|--|--|--|
| DIN EN 60204-1 | Electrical equipment at machinery | | | | |
| VDE 0113 Part 1 | General requirements | | | | |
| DIN EN 60439-1 VDE 0660 Part 500 | Low-voltage switchgear assemblies | | | | |
| DIN IEC 60-1, HD 588.1 VDE 0432 Part 1 | High-voltage test methods | | | | |
| DIN EN 60335-1 | Safety tests for household appliances | | | | |
| DIN VDE 0700-1 | Part 1: Safety of electrical devices for | | | | |
| | household use and similar purposes | | | | |
| DIN VDE 0701-1/5.93 | Repair, modification and testing of electrical devices – General requirements | | | | |
| DIN VDE 0701-200/6.88 | Mains powered electronic devices and accessories for household use and similar, general applications | | | | |
| DIN VDE 0701-240/4.86 | Safety requirements for data processing systems and office machinery | | | | |
| DIN VDE 0701-260 | Hand-held electric tools | | | | |
| DIN VDE 0472 | Testing cables and insulated conductors | | | | |
| DIN VDE 0404-2/7.88 | Devices for technical safety testing of electrical equipment – Devices for periodic testing | | | | |

Reference Conditions

Waveshape Sine (deviation between effective

and rectified value < 1%)

Ambient Temperature $+ 23 \, ^{\circ}\text{C} \pm 2 \, \text{K}$ Relative Humidity $40\% \dots 60\%$ Load Impedance Ohmic

Nominal Ranges of Use

Line Voltage 207 V ... 253 V Line Frequency 45 Hz ... 65 Hz

Line Voltage Waveshape Sine

Temperature Range 0 °C ... + 40 °C

Ambient Conditions

Storage Temperature $-20 \, ^{\circ}\text{C} \dots +60 \, ^{\circ}\text{C}$ Operating Temperature $-5 \, ^{\circ}\text{C} \dots +40 \, ^{\circ}\text{C}$ Accuracy $0 \, ^{\circ}\text{C} \dots +40 \, ^{\circ}\text{C}$ Relative Humidity Max. 75%,

no condensation allowed

Elevation to 2000 m

Power Supply

Line Voltage 207 V ... 253 V Line Frequency 45 Hz ... 65 Hz

Power Consumption 204: approx. 180 VA w/o accessories

204HP: max. 700 VA **204HV:** max. 100 VA

Max. Leakage Current 0.5 mA basic device and 204HP or HV Current Consumption Max. 6 A basic device and 204HP or HV

RS 232 Data Interface

Type RS 232C, serial, per DIN 19241

Data Format 9600, 8, N, 1

Connector 9-pin subminiature socket connector

Electrical Safety

Safety Class 204: II 204HP/HV: I

per IEC 61010-1/

. EN 61010-1 and VDE 0411-1

Nominal Voltage 230 V Test Voltage, 204 5.55 kV 50 Hz

Test Voltage, 204HP/HV Mains /PE / key switch /

external signal lamps to

high voltage measuring terminals:

204HP: 5 kV AC 50 Hz **204HV:** 8 kV AC 50 Hz

Mains to PE: 1.5 kV AC

Mains to external signal lamps:

2.3 kV AC (type test)

Measuring Category II
Contamination Degree 2

Safety Shutdown if i

Fuses 204:

if instrument overheats

Mains: T 1.6 / 250 Test probe: T16 / 1000

204HP/HV:

Mains: F 3.15 / 250

PROFITEST 204

Tester for DIN EN 60204 and VDE 0113

Electromagnetic Compatibility EMC PROFITEST 204

Product standard EN 61326-1: 1997

EN 61326: 1997/A1: 1998

| Interference Emission | | Class |
|-----------------------|-------------------------|---------------------|
| EN 55022 | | А |
| Interference Immunity | Test Value | Performance Feature |
| EN 61000-4-2 | Contact/Atmos 4 kV/8 kV | А |
| EN 61000-4-3 | 10 V/m | В |
| EN 61000-4-4 | Mains Connection - 2 kV | В |
| EN 61000-4-5 | Mains Connection - 1 kV | A |
| EN 61000-4-6 | Mains Connection - 3 V | A |
| EN 61000-4-11 | 0.5 Period / 100 % | А |

Mechanical Design

Display Multiple dot matrix display

128 x 128 pixels

Protection IP 40 per DIN EN 60529 /

VDE 0470 part 1

Extract from table on the meaning of IP codes

| IP XY | Protection against foreign object entry | IP XY | Protection against the |
|---------------------------|---|---------------------------|------------------------|
| (1 st digit X) | | (2 nd digit Y) | penetration of water |
| 4 | \geq 1.0 mm dia. | 0 | not protected |

Dimensions 204: (WxDxH)

255 mm x 133 mm x 240 mm

204HP/HV:

254 mm x 130 mm x 285 mm overall height, mounted on caddy: 380 mm x 250 mm x 650 mm 204: approx. 5.1 kg

Weight **204:** approx. 5.1 kg **204HP/HV:** approx. 8 kg


Standard Equipment

- 1 PROFITEST 204 test instrument with data interface (RS 232) and CENTRONICS port for external printer
- 1 test probe with integrated control panel for remote control of protective conductor and insulation measurement functions, with permanently attached measurement cable
- 1 test probe with integrated fuse and permanently attached measurement cable
- 1 cable lug
- 1 power cable with earthing contact plug
- 1 CD ROM with download program for report forms
- 1 maker's calibration certificate
- 1 RS232 bus cable for connecting the COM interface
- 1 operating instructions
- 1 PC software WinProfi for communication with PROFITEST 204. The PS3 CD-ROM includes the software WinProfi with the following content and functions:
 - up-to-date test instrument software
 - for loading other user interface languages
 - for loading firmware version updates
 - Exchange of measured data between test instrument and PC
 - Preparation and modification of templates for test reports at the PC, transfer of templates from PC to test instrument
 - Preparation, print-out and filing of test reports at the PC

Sample Displays, Menu-Driven Instrument Operation:



Protective conductor Insulation resistance Leakage current Voltage measurement High Voltage test



(i) Prot. conductor

The continuity of the protective conductor system is tested with a 10A 50Hz PELV source for a duration of 10s.

MENU, (i) Exit HELP STRRT Start Test Protective conductor

Setting the test parameters

Duration : 10.0s

Limit value: 1.00V

Diameter of Ø>6.0 mm²

MENU Cont. VA Change val.

START Start test ①HELP

PROFITEST 204

Protective conductor
Insulation resistance
Leakage current
Voltage measurement
High Voltage test

Insulation resistance R_{INS} 1.28G Ω U_{INS} 1.05 kV

Insul. resistance

(ﷺ The insulation
resistance is measured at 500V DC
between power
circuits and protective earth conductor.
It must exceed 1MΩ.

MENU, () Exit HELP STRRT Start test Insulation resistance

Setting test parameters

| Nom volt. : 1.00 kV | | Limit : 1.00 MΩ

MENU Cont. ▼▲Change val. STRRT Start test ①HELP

PROFITEST 204 Accessories

Expanded Features for PROFITEST 204HP-2.5kV and 204HV-5.4kV

- Test voltage selectable in 50 V steps
- Rise time (ramp) adjustable from 0.1 to 99 s
- Test duration adjustable from 1 to 120 s
- Floating test voltage outputs
- Electronically controlled test sequence
- Test sequence can be started with test pistol
- Breakdown voltage display
- Pulse-arc operation
- Phase angle display
- Measured values can be saved to memory
- Acoustic and optical error messages
- Key switch for protection against unauthorized start-up
- Connector terminals for external signal lamps

Expanded Features for PROFITEST 204HP-2.5kV

- Voltage test per EN 60204 / VDE 0113
- Test power: 500 VA (intermittent)
- Breaking current adjustable in 1 mA steps

Expanded Features for PROFITEST 204HV-5.4kV

- Test power: 50 VA
- Breaking current adjustable in 0.5 mA steps

Both of the high-voltage components, either of which can be mounted to the bottom of the basic instrument, allow for high-voltage testing. Voltage, current and phase angle are measured with permanently attached measurement cables. The bidirectional infrared interface at the base of the PROFITEST 204 is used for controlling the high-voltage component, as well as for uploading measured values to the basic instrument.

Technical Data, PROFITEST 204HP-2.5kV


| | Nominal Range of Use | Resolu- tion | Measuring Error | Intrinsic Error |
|----------------------|----------------------|-----------------|-------------------|--------------------|
| Test Voltage U AC | 250 V 2.5 kV | 1 V 10 V | ±(5% rdg. + 5 d) | ±(2.5% rdg. + 5 d) |
| Meas. Quantity | | | | |
| Current I AC | 10.0200 mA | 0.1 mA 1 mA | ±(7 % rdg. + 5 d) | ±(5% rdg. + 5 d) |


Technical Data, PROFITEST 204HV-5.4 kV)


| | Nominal Range of Use | Resolu- tion | Measuring Error | Intrinsic Error |
|----------------------|--------------------------------|-------------------|------------------------|--------------------------|
| Test Voltage U AC | 650 V1.00 kV 1.00 kV5.35 kV | 10 V | +27% rdg. +25% rdg. | 0 –5% rdg. 0 –3% rdg. |
| Meas. Quantity | | | | |
| Current I AC | 1.0 10.0 mA | 0.01 mA 0.1 mA | ±(7 % rdg. + 5 d) | ±(5 % rdg. + 5 d) |

Sample Displays, Menu-Driven Instrument Operation:










Extension PROFITEST 204HP...



Signal 204



Signal lamp set for high-voltage testing in accordance with DIN VDE 0104.



PROFITEST 204

Tester for DIN EN 60204 and VDE 0113

SECUTEST SI

The alphanumeric keypad allows for the entry of descriptions for each individual system. These descriptions are automatically saved to memory along with the appropriate data record. The SI module is screwed into the lid of the PROFITEST 204 for space-saving storage.



Caddy 204



PS3 Intelligent Modular Software for Test Instruments

Measurement data acquired with test instruments is transferred to PS3 and are then automatically assigned to activities such as testing, maintenance or inspection. Ready-to-sign test and work reports can thus be prepared with a minimum of effort.

The basic module and the device module are sufficient for standard requirements such as reading in measurement data and report printing.

Additional requirements such as following up on deadlines, test data history, data selection and list generation, right on up to complete object management (devices and buildings) with inventory management, errors indication, work orders and repairs are handled with the expansion module and with add-on modules. An overview of all of the features included with this software is given on our website.

System requirements for PS3

- a Windows compatible PC with at least a Pentium IV CPU
 2 GHz
- Windows 2000 SP4 / Windows XP
- working memory: 512 MB RAM
- a hard disc with approx. 800 MB free memory (without data)
- CD-ROM drive
- e-mail connection for loading control and/or clearing files

Remote 204 (Windows Software)


Control programming software for PROFITEST 204, 204L, 204HP, 204HV tester

Instead of starting individual tests manually, you can perform automatic test sequences with the PROFITEST 204/MetraMachine 204 tester by means of the PC software Remote 204.

This includes the creation of control files, the execution of the tests in accordance with the control files, the preparation of test reports as well as the export of data. The format supported by the software is easy to read in and process by all common spread-sheet programs.

In detail, Remote 204 includes the following functions:

- 3 different user interface languages are offered for choice,
- 2 serial ports are supported for activation of the PROFITEST 204.
- read out information on the test instrument,
- select control file for the test,
- · create new control files or modify existing ones,
- perform tests automatically by menu control mode,
- · skip, interrupt and continue tests,
- prepare new report templates or modify existing ones,
- store test data either manually or automatically,
- · print test data in test reports,
- convert data into a common spreadsheet format,
- display online user manual,
- control files of the DOS program PROFI SPS 204 can be used.



PROFITEST 204

Tester for DIN EN 60204 and VDE 0113

Order Information

| Designation | Туре | Article number |
|--|---------------------------|--------------------|
| Device for tests in accordance with VDE 0113 / EN 60204 with RS232 interface and CENTRONICS port for external printer, 2 test probes firmly connected via measuring cables with a length of 4 m, 1 plug-on cable lug, power cable with earthing contact plug, test report, operating instructions, PS3 CD-ROM containing the PC software Winprofi for loading another user interface language into the test instrument, for updating the test instrument firmware, for preparing test report templates at the PC and transferring them to the test instrument as well as for completing, storing and printing out test reports from the PC | PROFITEST 204 | GTM 5027 000 R0001 |
| Same test instrument as PROFITEST 204, however, with firmly connected measuring cable with a length of 12 m with START/MEMORY operation in the test plug | PROFITEST 204L | M505C |
| Sets | | |
| Complete system for tests in accordance with DIN EN 60204-1/VDE 0113 part 1, consisting of: PROFITEST 204, PROFITEST 204HP, Signal 204, Leadex 204, Caddy 204, test report | MetraMachine 204/2.5 | M504D |
| Complete system for tests in accordance with DIN EN 60204-1/VDE 0113 part 1, consisting of: PROFITEST 204, PROFITEST 204HP, Caddy 204, test report | MetraMachine 204-I/2.5 | M504E |
| Complete system for tests in accordance with DIN EN 60 439-1/VDE 0660 part 500, consisting of: PROFITEST 204, PROFITEST 204HV, Signal 204, Leadex 204 and Caddy 204, test report | MetraMachine 439/5.4 | M504F |
| Extensions | | |
| Special variant, High-voltage component to 2.5 kV | PROFITEST 204HP- 2.5kV | M505A |
| Special variant, High-voltage component to 5.4 kV | PROFITEST 204HV- 5.4kV | M505B |
| SI-Modul including batteries and operating instructions | SECUTEST SI | M702F |
| PC Software | | |
| Software for maintenance and electronic equipment management | PS3 | |
| Basic module and device driver, allows for read-out of the measured values from the PROFITEST 204, PROFITEST®0100S-II, PROFITEST®C, METRISO®C and | 200 014 | |
| SECUTEST® test instruments | PS3 GM | Z530E |

| Designation | Туре | Article number |
|---|------------------------------|--------------------|
| Device modules, basic module and add-on module complemented by the following modules — electronic equipment management — remote | | |
| maintenance management barcode printing | PS3 AM | Z531N |
| Control programming software in 3 languages for remote-control of PROFITEST/MACH 204 from the PC | Remote 204 | Z532A |
| PC software for the generation of reports and lists in addition to MS WORD; user languages: German/English | PC.doc-WORD™ ^{D)} | Z714A |
| PC program for the management of test data in addition to MS Access; user languages: German/English | PC.doc-ACCESS™ ^{D)} | Z714B |
| Upgrade of PC.doc win/med to PC.doc-WORD™ | PC.doc upgrade | Z714C |
| Accessory equipment | | |
| RS232 interface cable, 2 m | Z3241 | GTZ 3241 000 R0001 |
| Adapter for SL /ISO tests with PROFITEST 0100S-II and PROFITEST 204 | Adapter 701 | Z501F |
| Signal lamp set for high-voltage testing in accordance with DIN VDE 0104 | Signal 204 | Z504D |
| Plug-on cable lug for secure attachment of the test probe to the terminals | Kabelschuh 204 | Z504E |
| 12 m extension cable for use with the measuement cable and test probe with integrated measuring circuit fuse | Leadex 204 | Z504C |
| Transport caddy for PROFITEST 204 and 204HP/HV, including rubber straps for securing test cables and protective cover | Caddy 204 | Z504A |
| EMERGENCY STOP switch for PROFITEST 204HP/HV | STOP 204 | Z504F |
| For securing sites against unauthorized presence during high-voltage testing | Claim 204 | Z504G |
| Interface adapter for keyboards | PROFI-MFII | Z504H |
| Pack of 10 rolls recording chart for PSI module (1 roll = approx. 6.7 m) | PS-10P | GTZ 3229 000 R0001 |
| Pack of 10 ink ribbon cartridges for PSI module | Z3210 | GTZ 3210 000 R0001 |
| Universal carrying bag (for PROFITEST 204 and SECUTEST without HV-module) | F2000 ^{D)} | Z700D |

D) Data sheet available

For additional information on accessories, please refer to

- our Measuring Instruments and Testers Catalog
- our website www.gossenmetrawatt.com

Edited in Germany ullet Subject to change without notice ullet A pdf version is available on the internet