














Amp	Volt	Hz	IP Ident. colour + h	Part No.	Couplers	2 P + 	 	EAN-No. 4015609...																								
																																
					Couplers																											
					IEC/EN 60 309																											
																																
					flexible cable entry																											
																																
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>Øe</th> <th>f</th> <th>m</th> <th>Øp</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>154</td> <td>51</td> <td>68</td> <td>109</td> <td>7/13</td> </tr> <tr> <td>32 A</td> <td>196</td> <td>72</td> <td>91</td> <td>141</td> <td>11/24</td> </tr> <tr> <td>63 A</td> <td>266</td> <td>96</td> <td>114</td> <td>196</td> <td>15/33</td> </tr> </tbody> </table>				Ampère	d	Øe	f	m	Øp	16 A	154	51	68	109	7/13	32 A	196	72	91	141	11/24	63 A	266	96	114	196	15/33
Ampère	d	Øe	f	m	Øp																											
16 A	154	51	68	109	7/13																											
32 A	196	72	91	141	11/24																											
63 A	266	96	114	196	15/33																											
16	230 110 400	50/60 50/60 50/60	6 4 9	310 306 310 304 310 309	10/60 150	015528 015504 015559																										
32	230 110 400	50/60 50/60 50/60	6 4 9	330 306 330 304 330 309	10 280	016624 016617 016648																										
63	230 110 400	50/60 50/60 50/60	6 4 9	360 306 360 304 360 309	5 672	017515 017508 017522																										
																																
					inverted cable entry																											
																																
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>Øe</th> <th>f</th> <th>m</th> <th>Øp</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>121</td> <td>51</td> <td>68</td> <td>106</td> <td>8/15</td> </tr> </tbody> </table>				Ampère	d	Øe	f	m	Øp	16 A	121	51	68	106	8/15												
Ampère	d	Øe	f	m	Øp																											
16 A	121	51	68	106	8/15																											
16	230 110 400	50/60 50/60 50/60	6 4 9	315 306 315 304 315 309	10 140	016297 016280 174638																										
					<u>4109685</u>																											
																																
					gland entry																											
																																
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>Øe</th> <th>f</th> <th>m</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>135</td> <td>51</td> <td>68</td> <td>110</td> <td>13,5</td> </tr> <tr> <td>32 A</td> <td>171</td> <td>72</td> <td>91</td> <td>136</td> <td>21</td> </tr> <tr> <td>63 A</td> <td>255</td> <td>96</td> <td>114</td> <td>194</td> <td>36</td> </tr> </tbody> </table>				Ampère	d	Øe	f	m	Pg	16 A	135	51	68	110	13,5	32 A	171	72	91	136	21	63 A	255	96	114	194	36
Ampère	d	Øe	f	m	Pg																											
16 A	135	51	68	110	13,5																											
32 A	171	72	91	136	21																											
63 A	255	96	114	194	36																											
16	230 110 400	50/60 50/60 50/60	6 4 9	311 306 311 304 311 309	10 147	015931 015917 015948																										
32	230 110 400	50/60 50/60 50/60	6 4 9	331 306 331 304 331 309	10 265	016938 016921 016945																										
63	230 110 400	50/60 50/60 50/60	6 4 9	361 306 361 304 361 309	5 656	017713 017706 017720																										
125	see page 2/129		 IP67																													
																																
					couplers, suspension type, gland entry																											
																																
					<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>Øe</th> <th>f</th> <th>m</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>32 A</td> <td>180</td> <td>72</td> <td>91</td> <td>136</td> <td>21</td> </tr> </tbody> </table>				Ampère	d	Øe	f	m	Pg	32 A	180	72	91	136	21												
Ampère	d	Øe	f	m	Pg																											
32 A	180	72	91	136	21																											
32	230 110 400	50/60 50/60 50/60	6 4 9	334 306 334 304 334 309	10 274	017140 160631 160648																										