

Regular Grade

Anti-Seize & Lubricating Compound

Product Description

Never-Seez® Regular Grade is a superior, anti-seize and extreme pressure lubricant formulated to protect metal parts against rust, corrosion and seizure. Copper and graphite particles in a special grease protect parts even in high heat, high pressure and corrosive environments.

Product Benefits

- Keeps parts working longer with less wear
- Minimizes parts replacement costs
- Enables faster disassembly when repairs are needed (even after exposure to high temperatures)
- Protects against carbon fusion
- Resists alkaline solutions, most chemical and acid vapors, road salt, steam, salt water, iodized water
- Prevents galling on steel to stainless steel, titanium, magnesium, and other hard metals

Product Applications


- Nuts, bolts, screws
- Pipe fittings
- Boom guides
- Valve assemblies
- Pump mountings
- Chain drives
- Machinery
- Shafts
- Gaskets
- Press fit assemblies
- Taps and drills
- Packing glands
- Metal fittings

Limitations

- Never-Seez® Regular Grade is not recommended for high speed bearings. Never-Seez® Red Bearing Lubricant is suggested for these applications.
- For temperature resistance to 2400°F (1316°C), use Never-Seez® Pure Nickel Special.
- For applications where the presence of copper is prohibited, use Never-Seez® Nickel Grade, Nuclear Grade or Never-Seez® Blue Moly.

Other Anti-Seize Lubricants

- Nuclear Grade, Nickel Special
- Pure Nickel Special
- High Temperature Stainless
- High Temperature Stainless, Nuclear Certified
- Blue Moly Lubricant
- Black Moly Lubricant
- Red Bearing Lubricant
- White Food Grade with PTFE
- High Temperature Bearing Lubricant
- Pipe Compound with Teflon®
- Lithium EP Grease
- Mariner's Choice
- Heavy Metal Free
- PetroChem Grade



Technical Specifications

Color	Silver Gray	
Temperature Range, °F (°C)	-297°F to 1800°F (-183°C to 982°C)	
Thickener Type	Lithium Soap	
Particle Size, mil (microns)	2 maximum (50 µ)	
Density (g/cm3)	1.15-1.24	
		ASTM Test Method
Flash Point, °F (°C)	475°F (246°C)	D-92
Copper Corrosion Test @ 212°F (100°C), 24 hrs.	No corrosion	D-130
Worked Penetration, 60 strokes @ 77°F (25°C)	260-310	D-217
NLGI Grade	1/2	D-217
Dropping Point, °F (°C)	360°F (182°C)	D-566
Water Washout, % loss @ 100°F	0.30	D-1264
	@ 175°F	2.10
Coefficient of Friction @ 167°F (75°C), Four Ball	0.06	D-2266
Torque Coefficient, k factor	0.13	
Four Ball EP	Load Wear Index	81
	Last Non-seizure Load (scar)	63 kgf (0.41 mm)
	Last Seizure Load (scar)	400 kgf (1.87 mm)
	Weld Load	500 kgf

Electrical Properties

	Dissipation Factor	Dielectric Constant	Resistivity OHMS-cm	Conductivity Mhos/cm
Cycles				
1,000	0.0255	14.6	4.2 x 10 ⁹	4.32 x 10 ⁻⁹
10,000	0.0310	13.4	3.5 x 10 ⁹	3.77 x 10 ⁻¹⁰

© Teflon is a Registered Trademark of Dupont.

Specifications: Meets MIL-A-907; Ford Spec. #ESE-M12A4-A; G.E. D6Y28; Garrett PCS5724; U.T. Pratt & Whitney PWA 36053-2.

Ingredients: Contains a special, high-quality grease with graphite, copper flake, aluminum powder and zinc oxide.

Shelf Life: Never-Seez® Regular Grade does not deteriorate with age when stored unopened at temperatures below 120°F (49°C). Quality and performance are guaranteed for five years from the date of manufacture on unopened containers.

How Never-Seez Regular Grade Affects Torque:

Compared to unlubricated fasteners, the use of Never-Seez “Regular-Grade” can be viewed 2 ways:

- (1) It provides up to 30% MORE clamping force when applying the SAME amount of torque!
- (2) It provides the SAME clamping force when applying up to 30% LESS torque!

IMPORTANT!

- In order to best represent typical torque reduction values, Bostik references a “K-Factor” for unlubricated carbon steel fasteners of 0.185.
- Proper torque is critical and, if not clearly understood, users may over-torque their fasteners which may lead to costly damage. BOSTIK is not liable for any damages incurred. Refer to the Bostik standard warranty for details.

Use in accordance with Material Safety Data Sheet.

Ordering Information:

NEVER-SEEZ® REGULAR GRADE ANTI-SEIZE AND LUBRICATING COMPOUND

STOCK NUMBER	DESCRIPTION	SIZE
NS-160	Flat Top	1 lb.
NS-168	Flat Top	8 lbs.
NSA-16	Aerosol Spray	16 oz.
NSBT-4	Brush Top	1/4 lb.
NSBT-8	Brush Top	8 oz.
NSBT-16	Brush Top	1 lb.
NSC-1	Cartridge	1 lb.
NS-10	Tube	1 oz.
NSB-4	Tube	1/4 lb.
NS-42B	Pail	42 lbs.
NS-130B	Drum	130 lbs.
NS-425B	Drum	425 lbs.

Bostik, Inc.
211 Boston Street
Middleton, MA 01949 USA
Customer Service or Technical
Service: 1-800-7/BOSTIK
FAX: 978-750-7293
www.bostik-us.com

IMPORTANT NOTICE

All statements, technical information and recommendations set forth herein are based on tests which Bostik, Inc. believes to be reliable. However, Bostik does not guarantee their accuracy or completeness. The buyer should conduct its own tests of this product before use to determine proper preparation technique and suitability for proposed application. Any sales of this product shall be on terms and conditions set forth on Bostik's order acknowledgment. Bostik, Inc. warrants that the product conforms with Bostik's written specifications, and is free from defects. BOSTIK, INC. DISCLAIMS ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. THE BUYER'S SOLE REMEDY FOR NONCOMPLIANCE WITH THIS WARRANTY SHALL BE FOR THE REPLACEMENT OF THE PRODUCT OR REFUND OF THE BUYER'S PURCHASE PRICE. IN NO CASE WILL BOSTIK BE LIABLE FOR DIRECT, CONSEQUENTIAL ECONOMIC OR OTHER DAMAGES.

N20-062008