



| REV. | MODIFICATION. | DATE     | DRN |
|------|---------------|----------|-----|
| A    | NEW DWG       | 12/05/94 | PTG |
| B    | SCN03-075     | 29/04/03 | OW  |
| 03   | CO2010308     | 05/08/08 | SF  |




0.8[0.03] THICK DOUBLE SIDED ADHESIVE TAPE SEE TABLE FOR DETAILS

TYPICAL RELEASE TAB LOCATION


| PART NUMBER       | ADHESIVE                                      | "A"        | MATERIAL                  |
|-------------------|---|------------|---------------------------|
| MWSSEB-1-01A2-RT  | ACRYLIC ADHESIVE FOAM TAPE, PE LINER (RMS-24) | 9.5[0.37]  | NYLON 6/6 UL94-V2(RMS-01) |
| MWSSEB-1-19A2-RT  |   |            | NYLON 6/6 UL94-V0(RMS-19) |
| MWSSEBE-1-01A2-RT |   | 12.7[0.50] | NYLON 6/6 UL94-V2(RMS-01) |
| MWSSEBE-1-19A2-RT |   |            | NYLON 6/6 UL94-V0(RMS-19) |

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



ALL DIMENSIONS IN mm[Inch]  
 GENERAL TOLERANCES ±0.25  
 UNLESS OTHERWISE STATED  
 1 DECIMAL PLACE ±0.25  
 2 DECIMAL PLACES ± 0.10  
 ANGULAR ±1°

THIRD ANGLE



|  |                  |                |                    |                       |                     |
|--|------------------|----------------|--------------------|-----------------------|---------------------|
| MATERIAL:<br>SEE TABLE                               |                  |                | COLOUR:<br>NATURAL |                       |                     |
| DESCRIPTION:<br>MICRO WIRE SADDLE SIDE ENTRY ON BASE |                  |                |                    | PART No:<br>SEE TABLE |                     |
| DRG No:<br>0606-0002                                 |                  | NPR No:<br>N/A |                    | Mass:(g)<br>0.8       | SHEET SIZE<br>A4    |
| DRN<br>SF  | DATE<br>05/08/08 | CHKD<br>TC     | DATE<br>05/08/08   | SCALE<br>NTS          | SHEET No.<br>1 OF 1 |