


# Soldering Irons and Tips


## Electronically Controlled Low Voltage Soldering Irons



### SMD Adapter + Tips for LR 21, WP 80, WSP 80, WSP 80IG and MPR 80



Order No.	Model	Description
005 44 417 99	SMT	SMT Adapter for WSP 80




SMTA	SMTA	SMT Adapter for LR 21
------	------	-----------------------



SMT0504A	SMT0504A	A/1, for components 1,0 x 1,2 mm, 12 x 1,0 mm, 1,2 x 1,2 mm, 1,6 x 0,8 mm
----------	----------	---



SMT1206D	SMT1206D	D/1, for components 3,2 x 1,6 mm, 3,2 x 2,5 mm
----------	----------	--



SMT8K	SMT8K	K/2, for components 5,0 x 4,0 mm
-------	-------	----------------------------------

### Barrel for soldering irons WP 80 / WSP 80. For quick exchange of hot soldering tip

Unused tip will be placed in the safety rest inside the barrel.



Order No.	Description
005 87 447 10	Barrel for soldering iron WSP 80




005 87 448 45	Barrel short (40 mm) for WP 80 replacement
---------------	--



005 87 448 46	Barrel long (55 mm) for WP 80 replacement
---------------	---

### LT Soldering Tips for Robot Application

Soldering tips with twist lock. Only for use with robot application.



Order No.	Model	Description	Width A	Thickness B	Length
005 44 441 99	LTR A	Chisel tip	1,6 mm	0,8 mm	17,0 mm
005 44 422 99	LTR B	Chisel tip, 1,5 mm, wettable	2,4 mm	0,8 mm	17,0 mm
005 44 422 71	LTR B	Chisel tip, 6 mm, wettable	2,4 mm	0,8 mm	17,0 mm
005 44 433 99	LTR C	Chisel tip	3,2 mm	0,8 mm	17,0 mm

005 87 447 38	HER	Heating Element WSP 80 for Soldering Robot Application with PUD 81R and PUD 151R (page 74)
---------------	-----	--