

WIRE MANAGEMENT PRODUCTS

ZIPPER TUBING

ZIP-41

UL STANDARD 224
RoHS COMPLIANT

CHOOSE ZIPPER TUBING FOR:

- Protection Against Flame, Chemicals and Abrasion

ZIPPER TUBING APPLICATIONS:

- Wire/Cable Bundling
- Cable Jacketing Protection

CHARACTERISTICS

OPERATING TEMPERATURE:

- 20°C to 105°C

COLOR DESCRIPTION:

- All Standard Packages: Black

PHYSICAL PROPERTIES:

- Tensile Strength: 2500 psi, (177 kg/cm²)
- Ultimate Elongation: 300%
- Wall Thickness: 0.020" (0,51mm)
- Track Thickness: (When Closed) 0.150 Inches (3,8mm)
- Flammability: Self-Extinguishing (UL VW-1)

CHEMICAL PROPERTIES:

- Fungus Resistance: No Growth

SPECIFICATIONS

- UL Standard 224
- MIL-I-631D
- RoHS Compliant

 Recognized Component
Underwriters Laboratories Inc.


 Passes UL VW-1 Flame Test
Underwriters Laboratories Inc.

 RoHS Compliant

WIRE, CABLE, HARNESS PROTECTION:

Alpha Zipper Tubing is designed to provide a professional finish to wiring installations by eliminating exposed wiring and providing added protection against flame, chemicals


and abrasion. With Zipper Tubing, it's possible to isolate any group of wires or cables quickly and easily, without the bother of tape wrapping.



Zipper Tubing is manufactured from the highest quality, high temperature, stabilized PVC. The combination of flame, oil, fungus and moisture resistance, coupled with excellent abrasion resistance, makes Zipper Tubing an ideal jacketing material for use in harsh environments.

Supplied flat on a spool for ease of storage and accessibility, Alpha Zipper Tubing is an ideal jacketing material for use in the production or repair of pre-wired harness assemblies.

Each package contains two plastic sliders (AB 395).



Loc-Trac® provides an effective closure that is ideal for use where the assembly will be subjected to random flexing.

Alpha Part No. and Size	Nominal Inside Diameter		Nominal Flat Width		Standard Package Spool Lengths (Ft.)
	Inches	mm	Inches	mm	
ZIP-41-1/2	1/2	12,7	2	50,8	25, 100
ZIP-41-5/8	5/8	15,8	2-3/8	60,3	25, 100
ZIP-41-3/4	3/4	19,0	2-3/4	69,8	25, 100
ZIP-41-7/8	7/8	22,2	3-1/8	79,8	25, 100
ZIP-41-1	1	25,4	3-9/16	90,4	25, 100
ZIP-41-1-1/4	1-1/4	31,7	4-1/8	104,7	25, 100
ZIP-41-1-1/2	1-1/2	38,1	4-7/8	123,8	25, 100
ZIP-41-1-3/4	1-3/4	44,4	5-5/8	142,8	25, 100
ZIP-41-2	2	50,8	6-3/8	161,9	25, 100
ZIP-41-2-1/4	2-1/4	57,1	7-1/2	190,5	25, 100
ZIP-41-3	3	76,2	10	254,0	25, 100