


# **Datamate**

### Power/Signal Connectors Female Crimp


- **▶** Fully shrouded contacts, standard and high power.
- With or without jackscrews.
- Polarised mouldings.
- 10A power contacts





2 x (No. of ways per row -1)

## **CRIMP TAIL WITH POWER CONTACTS**



CALCULATION				
Α	C + 29.1			
В	C + 23			
C	2 x (No. of signal contacts per row -1)			

## **CRIMP BARREL SIZE**

C + 15.1 C + 9

CRIMP TYPE	WIRE SIZE (AWG)	STRANDING (MM)	CRIMP TOOL SETTING	PULL-OFF FORCE (NEWTONS)
Small Bore	28	7/0.125	6	12.5
Small Bore	26	19/0.1	6	25.0
Small Bore	24	7/0.2	6	44.0
Large Bore	22	19/0.15	6	50.0
Power Crimp	20	19/0.2	8	85.0
Power Crimp	18	19/0.26	8	140.0

### **TOOLS**

Recommended Crimp Tool - M22520/2-01 Positioner - T5747

**Contact Insertion Tool** – Z80-280

See page 108.


Instruction sheets available.

# WIRE STRIPPING DETAILS



#### HOW TO ORDER





		FINISH			
٦		05	Gold		
	TOTAL NO. OF SIGNAL CONTACTS				
	M80-70X <b>27, 36, 45, 51, 63</b>				

M80-70X **27, 36, 45, 51, 63**M80-71X **06, 15, 24, 30, 42** 

#### www harwin com



















