



PCB LAYOUT



1. MATERIALS:

- a BODY: ZINC ALLOY, DIE CASTING NICKEL PLATED.
- b CONTACT: BRASS NICKEL PLATED.
- c BRACKET: A.B.S UL 94HB
- d INSULATOR: ENGINEER PLASTIC POM UL 94HB.

2. NOMINAL IMPEDENCE 50(75) OHMS.

3. FREQUENCY RANGE: 0-2 GHz.

4. MAX PEAK VOLTAGE: 500V.

5. DIELECTRIC STRENGTH WITHSTAND 1.5KV RMS FOR ONE MINUTE.

6. INSULATION RESISTANCE AT 500VDC 5000 MEGOHMS MIN.

ALPHA SWITCHES

NAME

TWO BNC FEMALE IN ONE ROW

PART NAME	料號	∠		SCALE	FIT	DESIGNED
MODEL NO.	SS-134 (1x2)	∠		FRACTIONS	±	DRAWING ALAN
DRAWING NO.	010134301	∠		DECIMALS	±D.16	CHECKED
FINISHING		∠	2002/06/11	A1	ANGLES	APPROVED
MATERIAL	SYM		DATE	REVISION	UNITS	MM