



Products

www.hellermannTyton.co.uk | Products | Cable Ties and Fixings | Cable Ties | Inside Serrated Cable Ties | T-Series |

T.I.P.S.
Webshop

Printview



PDF views

- Catalog page
- All catalog pages

T150M

111-15619



T18S – T255M



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

UL Listed (US and Canada)

TRUE

UL Recognized (US and Canada)

TRUE

Base Data

Application Method

Quick, simple fixing by hand or with HellermannTyton tensioning tools

Colour

Natural (NA)

Label E-Number Norway

13 447 14

Local Order Number

T150M.NN1P

Recommended Application Tool

MK6, MK6PN, MK9, MK9HT

Logistic and Packaging

Carton Quantity

1 pcs.

EAN code

4031026274911

Package Content

25

Quantity of Europallet

12000 pcs.

Quantity per

Bag

UPC

08930606372

Weight (kg) (Metric)

8.4 kg

Material and Specifications

CSA Certified

FALSE

Flammability

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

Product Dimensions

Bundle Diameter max (Imperial)

5.91 "

Bundle Diameter max (Metric)

150 mm

Bundle Diameter min (Imperial)

.31 "

Bundle Diameter min (Metric)

8.0 mm

Length L (Imperial)

21.00 "

Length L (Metric)

530 mm

Minimum Tensile Strength (imperial)

175 lbs

Minimum Tensile Strength (N)

780 N

Width W (Imperial)

.35 "

Width W (Metric)

8.9 mm