

Desk Top Power Supplies

POWER
SOLVE

www.powersolve.co.uk

PSE15 Series 15 Watts Switch Mode Universal AC Input

The PSE15 Series is a range of plastic fully sealed, splash proof, desk top power adaptors. All units are UL94V-1 compliant and carry full UL, cUL (UL60950) and TUV/GS (EN60950) safety approvals. All models are 100% tested and burned in.



Features

- Single output
- Optional output connectors
- Optional inlet connectors
- 100% Burn-in
- Wide input voltage range 90 to 264 VAC
- Input surge current protection
- Overcurrent protection

Electrical Specification

INPUT

Input voltage	90-264 VAC
Input frequency	47-63 Hz
Input current	0.4A (rms) for 115 VAC, 0.26A (rms) for 230 VAC
Safety ground leakage	current 0.75mA max @ 240 VAC 50Hz

OUTPUT

Output voltage	See rating chart
Output current	See rating chart
Output power range	0 to 15 watts
Ripple	1% Typical 2% Max
Overcurrent protection	All outputs protected to short circuit condition
Temperature coefficient	All outputs $\pm 0.04\%$ / °C maximum
Transient response	4mS full load to half load, 100 VAC Input

ENVIRONMENTAL

Operating temperature	0°C to +70°C, derate linearly above 40°C to 50% @ 70°C
Storage temperature	-40°C to +85°C
Relative humidity	5% to 95% non-condensing

GENERAL

Efficiency	75% Typical
Hold-up time	5 msec minimum
Line regulation	$\pm 0.5\%$ maximum at full load
Insulation resistance	50 Mohm minimum from output to ground
Withstand voltage	3000 VAC from input to output 1500 VAC from output to ground
MTBF	100,000 hours minimum at full load at 25°C ambient
EMI requirements	Meets conduction limits of (a) FCC PART 15 CLASS B (b) CISPR CLASS B
Safety Approvals	UL/cUL60950, TUV/GS (EN60950)

Desk Top Power Supplies

**POWER
SOLVE**

www.powersolve.co.uk

Output Voltage/Current Rating Chart - PSE15 Series

MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	MAX OUTPUT POWER
PSE15-133A	3.3VDC	2.5 Amp	12 Watts
PSE15-105A	5VDC	2.5 Amp	12 Watts
PSE15-209A	9VDC	1.66 Amp	15 Watts
PSE15-312A	12VDC	1.25 Amp	15 Watts
PSE15-516A	16VDC	0.94 Amp	15 Watts
PSE15-518A	18VDC	0.83 Amp	15 Watts
PSE15-624A	24VDC	0.63 Amp	15 Watts
PSE15-848A	48VDC	0.31 Amp	15 Watts

Models above are standard ex-stock items with 3 pin IEC 320 inlet connector (Fig 1). Output Lead is 1.8 Metre long fitted with a 2.1 x 5.5 x 11mm Female Barrel Connector, wired centre positive.

Options: Alternative input connectors as per drawings below. Models are suffix B for 2 pin input (fig 2), C for alternative 3 pin input (fig 3) and D for lead in lead out version (fig 4). i.e. PSE15-105(A, B, C or D)

Alternative output connectors available, consult sales office with your requirements

Any output voltage is available within the range of 3V to 48V DC

Some of these may be subject to minimum order quantities.

MECHANICAL DIMENSIONS mm

