Proximity Sensors Capacitive Flat pack Polycarbonate Housing Type EC 5525, DC







- Featuring *TRIPLESHIELD*™ sensor protection
- Adjustable sensing distance 4-25 mm
- Rated operational voltage: 10-40 VDC
- Output: DC 200 mA, NPN or PNP
- Make and break switching function, LED indication
- Capacitive, Inductive and Photoelectric flat pack series in PC housing, IP 67
- High noise immunity

Connection type

- Universal flush and non-flush mountable
- Plug and cable versions

Product Description

Capacitive proximity switches with sensing distance 16 mm flush mounted and sensing distance 25 mm non-flush mounted by adjustment. 4-wire DC output with both make (NO) and break (NC)

switching. Flat pack housing, size (WxHxD) 35 x 55 x 15 mm made in polycarbonate. Easy mounting with only two M4 screws. Ideal for use in material handling and plastic machinery applications.

Capacitive proximity switch Housing Rated operational distance Output type Housing material

Type Selection

Housing dimensions W x H x D	Rated operating dist. (S _n) ¹⁾ Flush/non-flush	Ordering no. NPN/cable Make & break swit.	Ordering no. NPN/plug Make & break swit.	Ordering no. PNP/cable Make & break swit.	Ordering no. PNP/plug Make & break swit.
35 x 55 x 15	16/25 mm	EC 5525 NPAP	EC 5525 NPAP-1	EC 5525 PPAP	EC 5525 PPAP-1

¹⁾ Object: Grounded steel plate


Specifications

Rated operating dist. (S _n)	4 to 25 mm factory set at 25 mm	Frequency of operati cycles (f)	
Sensitivity	Adj. 270° single turn pot.meter	Indication for output	
Effective operating dist. (S _r)	$0.9 \times S_n \le S_r \le 1.1 \times S$	Environment	
Usable operating dist. (S _u)	$0.8 \times S_r \le S_n > 1.2 \times S_r$	Degree of protection	
Repeat accuracy (R)	≤5%	Temperature	
Hysteresis (H)	3 to 20% of sensing distance	Operating temperature Storage temperature	
Rated operational volt. (U _B)	10 to 40 VDC (ripple included)	Housing material	
Ripple	≤ 10%	Connection Cable	
Rated operational current (I _e) Continuous	≤ 200 mA	Plug (-1)	
No-load supply current (I _o)	≤ 10 mA (no load)	Cable for plug (-1)	
Voltage drop (U _d)	≤ 2.5 VDC at max. load	Weight (incl. nuts)	
Protection	Reverse polarity, short-circuit, transients	Approvals CE-marking	


Frequency of operating cycles (f)	50 Hz	
Indication for output ON	LED, yellow	
Environment		
Degree of protection	IP 67 (Nema 1, 3, 4, 6, 13)	
Temperature		
Operating temperature	-25 to +80°C (-13 to +176°F)	
Storage temperature	-40 to +85°C (-40 to +185°F)	
Housing material	Polycarbonate (PC), grey	
Connection		
Cable	Grey, 2 m, 4 x 0.34 mm ²	
	Oil proof, PVC	
Plug (-1)	M12 x 1	
Cable for plug (-1)	CON.1A-series	
Weight (incl. nuts)	125 g (cable version)	
,	40 g (plug version)	
Approvals	UL, CSA	
CE-marking	Yes	
-		




Dimensions



Wiring Diagrams






Adjustment Guide

The environments in which capacitive sensors are installed can often be unstable regarding temperature, humidity, object distance and industrial (noise) interference. Because of this, Carlo Gavazzi offers as standard features in all TRIPLESHIELD™ capacitive sensors a user-friendly sensitivity adjustment instead of having a fixed sensing range, extended sen-

sing range to accommodate mechanically demanding areas, temperature stability to ensure minimum need for adjusting sensitivity if temperature varies and high immunity to electromagnetic interference (EMI).

Note:

Sensors are factory set (default) to maximum rated sensing range.



Installation Hints

Capacitive sensors have the unique ability to detect almost all materials, either in liquid or solid form. Capacitive sensors can detect metallic as well as non-metallic objects, however, their traditional use is for non-metallic materials such as:

- Plastic Industry
 Resins, regrinds or moulded products.
- Chemical Industry
- Cleansers, fertilisers, liquid soaps, corrosives and petrochemicals.
- Wood Industry

Saw dust, paper products, door and window frames.

Ceramic & Glass Industry
 Raw material, clay or finished products, bottles.

Packaging Industry Package inspection for level or contents, dry goods, fruits and vegetables, dairy products.

Materials are detected due to their dielectric constant. The bigger the size of an object, the higher the density of material, the better or easier it is to detect the object. Nominal sensing distance for a capacitive sensor is referenced to a grounded metal plate (ST37). For additional information regarding dielectric ratings of materials please refer to Technical Information.

Accessories

• Plugs CON.1A.. serie

For further information refer to "Accessories".

Delivery Contents

- Capacitive switch: EC55.. PAP(-1)
- Screw driver
- Packaging: Cardboard box
- Installation & Adjustment Guide