


Our smallest sensor.

F 10 laser sensors in a subminiature design.

Small but powerful.

The smallest laser sensor with adjustable background suppression.





Mini sensor with maximum user comfort: A comfortable start-up with electronic teach and clearly visible status LEDs – not to be be taken for granted in this sensor size.

FT 10 BGS – THE FLAGSHIP

- Subminiature sensor with laser light and adjustable background suppression
- Detection range up to 60 mm
- Precise and reliable switching performance even on changing object surfaces and colours
- Teach-in
- Bright or shiny background machine parts do not affect the switching performance



Small size, high performance: The F10 is the only subminiature sensor using laser light on the market. Its light spot is so sharp & accurate that small parts can be reliably detected, even at large distances. For example, the proximity switch with background suppression can easily detect a 0.5 mm diameter wire at a distance of 60 mm - it can therefore hold its own amongst the considerably larger models of its class.

The F10 does not just offer excellent performance data. Its unmistakable design also offers special features unique for its size. The dovetail mount facilitates fine adjustment in difficult locations and the M5 connector enables easy connection and sensor replacement. As you can see, we have done everything to ensure you get the most from our smallest sensor!


F 10 – HIGHLIGHTS AT A GLANCE

- Subminiature sensor for installation in tight spaces
- Bright, precise laser light spot for first-rate small-part detection and easy alignment
- Comfortable use via electronic teach key or control cable
- Ingenious mounting accessories for quick and simple integration
- Wide range of product versions to suit all requirements
- Robust, glass fibre reinforced plastic housing (IP67) with Ecolab accreditation
- Permanent, cleaning-resistant laser marking





M5 connector: The F 10 is available either with a M5 connector, with a pigtail cable (200 mm) and moulded M8 connector or with a fixed cable.



If the sensor is to be installed in a

cramped location, we recommend

the dovetail mounting bracket

that enables precision alignment

Easy installation:

of the sensor.

 $\pm 10^{\circ}$

14,6 mm 8 mm



21,1 mm

Special features:

The distinguishing features of the F10 are the glass fibre reinforced plastic housing with integrated mounting sleeve, the dovetail guide fitted at the back of the sensor and the permanent laser marked type designation.

Dovetail:

The dovetail bracket is inserted in the corresponding channel on the sensor housing and simplifies fine adjustment of the sensor.

3

Small but versatile.

There is always room for the F 10 sensor.

Applications

- in tight spaces
- in handling and assembly systems
- in large-scale integrated machines
- an alternative to fibre-optic amplifiers

Typical sectors

- Special purpose machine construction
- Semiconductor and electronics production
- Laboratory automation
- Pharmaceutical industry and medical technology
- Solar industry
- Packing machines
- Printing and paper industry electronics





Miniature lightweight:

Thanks to their miniature size and light weight, the sensors from the F 10 series are tailor-made for use in very cramped spaces or on moving machine parts, for example in large-scale integrated production machines or handling & assembly systems.

In many applications there is simply not enough room for conventional sensors but there is for F 10: it fits in almost every nook and cranny. Whether used in handling & positioning applications, in the production of solar cells or the assembly of semi-conductor components – an F 10 can achieve top performances even installed in tight spaces. The BGS proximity switch is only $21.1 \times 14.6 \times 8 \text{ mm}^3$ small and weighs just 3 grammes thus even fitting into robotic grippers where it literally carries no weight. With precise & adjustable background suppression, this sensor always triggers on the target even when bright or shiny machine parts are visible behind – something that typically affects the performance of many other sensors.

Thanks to their small dimensions and to their performance, laser sensors from the F 10 series open up completely new application potentials and make a credible alternative to – decidedly more expensive – fibre-optic amplifiers. When top performance is required in the tiniest space, F 10 is your sensor.

Small but smart.

A sensor whose every detail counts.

Different applications each require suitable sensors. The F 10 is available as a through-beam sensor, a retro-reflective light barrier and as a proximity switch with background suppression or fixed focus – making four different versions. All product versions are equipped with a red laser light, which has a high optical performance. The very bright light spot facilitates alignment in daylight and is not dangerous as the sensors are laser class 1.


Sensors from the F 10 series offer an impressive optical performance and a well thought out housing from the robust, glass fibre reinforced plastic body with permanent laser marking, the well-designed mounting details through to comfortable settings via an electronic teach key or control cable. Thanks to the three possible modes of connection: connector, cable and pigtail cable, installation is totally flexible. The comprehensive range of accessories meets every user requirement – the only thing we do not supply is a magnifying glass!



Bright but harmless laser light: The red laser light on the F10 produces a bright light spot which is clearly visible even by daylight. Thanks to laser class 1, the laser beam presents no user hazard.

ECOLAB

All F10 product versions have been awarded the Ecolab certificate and therefore fulfill the highest IP requirement with regard to wateringress and material resistance.



F 10 – Technical data 153-00894 14.6 Teach-in 8 2.8 LED 2 ED 1 Receiver 21.1 ې دې Emitter 18.3 8 03,2 5.7 M5x0.5 Light emitter/Light used Laser, red 655 nm Laser class 1 10 to 30 V DC Operating voltage Status display 2 LEDs (green/yellow) Housing material PUR • M5 connector Connection types • 2 m cable • Pigtail cable (200 mm) with moulded M8 connector Front panel material PMMA IP67 Protection Ambient temperature -20 to +50 °C in use -40 to +80 °C in storage

F 10 – Product overview						
	Proximity switch with adjustable background suppression		Proximity switch with background suppression (fixed focus)		Retro-reflective light barrier	Through-beam light barrier
	FT 10-RLH	FT 10-RLHR (wide beam)	FT 10-B-RLF1	FT 10-B-RLF2	FR 10-RL	FE 10-RL/ FS 10-RL
Detection range	2 60 mm	2 60 mm	2 15 mm	2 30 mm	-	-
Max. distance	-	-	-	-	0,1 2,5 m	0 5 m
Scanning range	-	-	-	-	0,1 2 m	0 3 m
Switching frequency	1000 Hz	1000 Hz	1000 Hz	1000 Hz	1000 Hz	10 kHz
Setting	Teach-in	Teach-in	-	-	Teach-in	Teach-in


Detailed technical data and order information is available at **www.sensopart.com**


7

We look ahead.

Yesterday, today and in the future.









SENSOR TECHNOLOGY



Since SensoPart was founded in 1994, we have constantly focussed on the future. Our motto has always been: We gauge ourselves not by what is possible today, but by our ideas for what can be achieved in the future. Many ground-breaking ideas from that time have since become successful products, which are now indispensible in modern automation technology – endorsed by the numerous prizes for innovation which we have received over recent years. Today, SensoPart is the technological leader in many areas of industrial sensor technology. And we still have many ideas for the future.

Light barriers Proximity switches Laser sensors Miniature sensors Distance sensors Colour sensors Contrast sensors Anti-collision sensors Slot sensors Fibre-optic amplifiers Inductive sensors Capacitive sensors Ultrasonic sensors

VISION

Vision sensors Smart cameras Object detection Object measurement Colour detection Code reading Lighting Lenses

Find the suitable product for your application under www.sensopart.com/ productfinder

Germany

SensoPart Industriesensorik GmbH Nägelseestraße 16 D-79288 Gottenheim Tel. +49 7665 94769-0 Fax +49 7665 94769-765 www.sensopart.de

France

SensoPart France SARL 11, rue Albert Einstein Espace Mercure F-77420 Champs – Marne la Vallée Tél. +33 164 730061 Fax +33 164 731087 www.sensopart.fr

Great Britain

SensoPart UK Limited Unit 12 – 14, Studio 1 Waterside Court, Third Avenue, Centrum 100, Burton on Trent DE14 2WQ Tel. +44 1283 567470 Fax +44 1283 740549 www.sensopart.com

USA

SensoPart Inc. 28400 Cedar Park Blvd Perrysburg OH 43551, USA Tel. +1 866 282-7610 Fax +1 419 897-7991 www.sensopart.com