

Wiha easyTorque.

Controls and works effectively.



With the easyTorque, assembling indexable inserts is safe and easy.



Pre-set, fixed torque value, easy to handle, robust design.



Robust and reliable: the integrated torque mechanism.

The easyTorque screwdriver with a pre-set, fixed torque setting is an ingenious development for controlled screw applications with a pre-set torque.

Used to assemble indexable inserts, it does its duty safely. The pre-set, fixed torque values are defined in accordance with the recommendations of high-profile manufacturers of indexable inserts.

As with its big brother, the TorqueFix®, the easyTorque handle can be combined with the colour-coded, interchangeable blades from the torque range. If a blade has worn out, it can easily be replaced in no time at all. This is practical and cost-effective. Typical for the easyTorque that offers best value for money.

When the pre-set torque value is attained, the integrated mechanism disengages completely. This prevents the over-tightening of the screw. Thanks to the robust industrial quality, the tool has a long service life and high functional safety. The opening torque is not mechanically limited in the anti-clockwise direction. Wiha offers ten torque handles in the 0.5 to 3.8 Nm range with a release accuracy of $\pm 10\%$.



Wiha easyTorque:

- Torque screwdriver with pre-set, fixed torque
- Robust industrial design
- Ergonomic handle with torque value printed on handle
- Interchangeable blades with colour coding
- Opening torque not mechanically limited
- Release accuracy $\pm 10\%$

easyTorque Torque Screwdriver.



NEW
291

easyTorque Torque Screwdriver.

With a Fixed Torque Value Ex-factory.

Handle:

Comfortable handle for good power transfer.

Lightweight design, torque value printed on tool.

Internal mechanism slips when torque value has been attained.

Opening torque not mechanically limited in anti-clockwise direction.

Release accuracy $\pm 10\%$.

Application:

Ideal for screw-fastening indexable inserts to a prescribed torque.

Order-No.	Nm	⊙	⊖	⊕	⊗	£
30342 6	0.5	4	103	32	1	29.30
30343 3	0.6	4	103	32	1	29.30
30344 0	0.9	4	103	32	1	29.30
30345 7	1.1	4	103	32	1	30.20
30346 4	1.2	4	103	32	1	30.20
30347 1	1.4	4	103	32	1	30.20
30348 8	2.0	4	103	32	1	30.20
30349 5	2.5	4	103	32	1	30.20
30350 1	3.0	4	103	32	1	31.00
30351 8	3.8	4	103	32	1	31.00

Wiha Torque Screwdrivers.

Torque Interchangeable Blades.



2859 Torque Slotted Interchangeable Blade. For Torque Screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Colour-coding: grey.

Standards: Tip DIN 5264, ISO 2380.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque handle.

Order-No.	⊖	⌀	⬮	↔	↔	max. Nm	🔩	£
26227 3	0.25	1.5	4	175	42	0.15	1	2.75
26228 0	0.4	2.0	4	175	42	0.4	1	2.75
26151 1	0.4	2.5	4	175	42	0.4	1	2.75
26277 8	0.5	3.0	4	175	42	0.6	1	2.75
26278 5	0.6	3.5	4	175	42	1.1	1	2.75
26279 2	0.8	4.0	4	175	42	2.5	1	2.75



2859 Torque Phillips Interchangeable Blade. For Torque Screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Colour-coding: dark blue.

Standards: Tip DIN ISO 8764-1.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque handle.

Order-No.	⊕	⬮	↔	↔	max. Nm	🔩	£
26199 3	PH000	4	175	42	0.9	1	2.75
26196 2	PH00	4	175	42	0.4	1	2.75
26197 9	PH0	4	175	42	0.4	1	2.75
26058 3	PH1	4	175	42	3.8	1	2.75
27079 7	PH2	4	175	42	5.5	1	2.75

Torque Interchangeable Blades.



2859 Torque Pozidriv Interchangeable Blade. For Torque Screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Colour-coding: light blue.

Standards: Tip DIN ISO 8764-1.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque handle.

Order-No.	⊕	⬮	↔	↔	max. Nm	🔩	£
26198 6	PZ0	4	175	42	0.9	1	2.75
26148 1	PZ1	4	175	42	3.8	1	2.75
26889 3	PZ2	4	175	42	5.5	1	2.75



2859 Torque Hex Interchangeable Blade. For Torque Screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Colour-coding: red.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque handle.

Order-No.	⦿	⬮	↔	↔	max. Nm	🔩	£
26200 6	1.5	4	175	42	0.9	1	2.75
26060 6	2.0	4	175	42	1.8	1	2.75
26061 3	2.5	4	175	42	3.8	1	2.75
26062 0	3.0	4	175	42	8.0	1	2.75
26063 7	4.0	4	175	42	8.0	1	2.75



2859 Torque Ballpoint Hex Interchangeable Blade. For Torque Screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Colour-coding: red.

Application: For applications where recommended torque settings are important. Use in combination with a Wiha torque handle.

Extra: The ballpoint enables the user to work at angles up to 25°.

Order-No.	⦿	⬮	↔	↔	max. Nm	🔩	£
26221 1	1.5	4	175	42	0.4	1	2.75
26222 8	2.0	4	175	42	0.9	1	2.75
26223 5	2.5	4	175	42	2.0	1	2.75
26224 2	3.0	4	175	42	3.8	1	2.75
26225 4	4.0	4	175	42	8.0	1	2.75

