


Features

- ◆ Highest power density in SIP package
- ◆ Ultra wide 4:1 input range
- ◆ Small footprint: 21.8 x 9.2 mm
- ◆ Temperature range -40° to +85°C
- ◆ High efficiency up to 81%
- ◆ Excellent load and line regulation
- ◆ Short-circuit protection
- ◆ I/O isolation 1500 VDC
- ◆ Remote On/Off control
- ◆ 3-year product warranty



The TMR-3WI series is a new family of isolated 3W DC/DC converters with regulated output, featuring ultra-wide 4:1 input voltage range. The product comes in an ultra-compact SIP plastic package with a small footprint occupying only 2.0 cm² (0.3 square in.) of board space. An excellent efficiency allows -40° to +85°C operation temperatures.

Further features include remote On/Off control and continuous short circuit protection. The very compact dimensions of these converters make them an ideal solution for many space critical applications in battery-powered equipment and instrumentation.

Models

Order code	Input voltage	Output voltage	Output current max.	Efficiency typ.
TMR 3-1210WI	4.5 – 18 VDC (12 VDC nominal)	3.3 VDC	700 mA	74 %
TMR 3-1211WI		5 VDC	600 mA	78 %
TMR 3-1212WI		12 VDC	250 mA	80 %
TMR 3-1213WI		15 VDC	200 mA	80 %
TMR 3-1221WI		±5 VDC	±300 mA	80 %
TMR 3-1222WI		±12 VDC	±125 mA	80 %
TMR 3-1223WI		±15 VDC	±100 mA	80 %
TMR 3-2410WI		9 – 36 VDC (24 VDC nominal)	3.3 VDC	700 mA
TMR 3-2411WI	5 VDC		600 mA	80 %
TMR 3-2412WI	12 VDC		250 mA	81 %
TMR 3-2413WI	15 VDC		200 mA	81 %
TMR 3-2421WI	±5 VDC		±300 mA	79 %
TMR 3-2422WI	±12 VDC		±125 mA	80 %
TMR 3-2423WI	±15 VDC		±100 mA	81 %
TMR 3-4810WI	18 – 75 VDC (48 VDC nominal)		3.3 VDC	700 mA
TMR 3-4811WI		5 VDC	600 mA	79 %
TMR 3-4812WI		12 VDC	250 mA	79 %
TMR 3-4813WI		15 VDC	200 mA	79 %
TMR 3-4821WI		±5 VDC	±300 mA	79 %
TMR 3-4822WI		±12 VDC	±125 mA	79 %
TMR 3-4823WI		±15 VDC	±100 mA	80 %

Input Specifications

Input current at full load	12 Vin models: 340 mA max. 24 Vin models: 170 mA max. 48 Vin models: 85 mA max.
Input current at no load	12 Vin models: 40 mA max. 24 Vin models: 25 mA typ. 48 Vin models: 15 mA typ.
Surge voltage (100 msec. max.)	12 Vin models: 25 V max. 24 Vin models: 50 V max. 48 Vin models: 100 V max.
Input filter	internal capacitor
ESD (electrostatic discharge)	EN 61000-4-2, air ±8 kV, contact ±6 kV, perf. criteria A
Radiated immunity	EN 61000-4-3, 10 V/m, perf. criteria A
Fast transient / Surge	EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 1 kV perf. criteria A With external input capacitor e.g. Nippon chemi-con KY 100 µF, 100 V, ESR 110 mOhm
Conducted immunity	EN 61000-4-6, 10 Vrms, perf. criteria A

Output Specifications

Voltage set accuracy	±1 % max
Regulation	– Input variation Vin min. to Vin max. 0.2 % max. – Load variation 0 – 100% single output models: 1.0 % max. dual output models: 1.0 % max. balanced load – Load cross regulation 25/100% 5.0 % max. (dual output models)
Minimum load	not required
Temperature coefficient	0.02 %/K
Ripple and noise (20 MHz Bandwidth)	30 mVpk-pk max.
Start up time (constant resistive load)	– Power On 30 ms typ. – Remote On 30 ms typ.
Transient response setting time (25% load step change)	250 µs typ.
Short circuit protection	continuous, automatic recovery
Capacitive load	3.3 VDC models: 1'760 µF max. 5 VDC models: 1'000 µF max. 12 VDC models: 170 µF max. 15 VDC models: 110 µF max. ±5 VDC models: ±470 µF max. ±12 VDC models: ±100 µF max. ±15 VDC models: ±47 µF max.

General Specifications

Temperature ranges	– Operating –40°C to +85°C – Case temperature +100°C max. – Storage –55°C to +125°C
Load derating	3.3 %/K above 70°C
Humidity (non condensing)	95 % rel. H max.
Reliability, calculated MTBF (MIL-HDBK-217F, @ 25°C, ground benign)	>1.7 Mio h

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

