



755 TORQUE SCREWDRIVER

Type FS

Use:

- ✔ Controlled screw tightening in the range 0.02 - 13.6 N·m
- ✔ Serial manufacture with constant tightening value
- ✔ Electronic industry, precision mechanics and industrial manufacturing

Features:

- ✔ Pre-set torque screwdriver without a scale
- ✔ With 1/4" female hexagon spindle for use with 1/4" hexagon bits as per DIN 3126 - C 6.3
- ✔ With adapter also suitable for 1/4" square drive sockets as per DIN 3124
- ✔ Actuation accuracy: +/- 6% tolerance of the set torque
- ✔ In accordance with DIN EN ISO 6789, traceable to national norms
- ✔ Precision radial ball clutch and cam design for controlled bi-directional tightening
- ✔ Precision mechanism slips very noticeably through when the set torque is reached
- ✔ Automatic resetting to the starting position
- ✔ Lightweight construction by virtue of anodised aluminium handgrips
- ✔ ESD (electrostatic discharge) = electrostatically protected
- ✔ The pre-setting can be made at the RAHSOL DREMOTEC factory or by the user on suitable torque testers
- ✔ If ordering, please specify the N·m value - if a fixed factory setting is desired (price on request)

Scope of delivery:

- ✔ 1/4" square/hexagon drive adaptor (no. 757-20)
- ✔ Operating instructions
- ✔ Test certificate as per DIN EN ISO 6789
- ✔ Delivered in sturdy cardboard packaging

Code	No.	Drive	cN·m	N·m	mm	Handgrip colour	Stk
1471481	755-01	⊕ + ⊕	2-22		76	red	50
1471473	755-02	⊕ + ⊕	0,5-22		104	golden	72
1471465	755-03	⊕ + ⊕	2-135		111	blue	210
1471457	755-04	⊕ + ⊕	6-406		127	green	280