

## Group 08 - HABERO

### 600 E-H Engineers' hammer ROTBAND-PLUS

Forged hammer head DIN 1041 made from high-quality special steel, black epoxy powder-coated. With contoured ash or hickory handle DIN 5111 additionally shaped with a long and hardened steel sleeve. The tapered collar, fixing plate and wood screw bond the hammer head and the handle into one unit. DBGM.G 9414 1878 (German utility patent), European-Patent-No. 0703045.



DIN 1041

Code	No.	L mm	🔧	🔧	PU
8581610	600 E-100	260	100	170	6
8581880	600 E-200	280	200	275	6
8581960	600 E-300	300	300	425	6
8582180	600 E-400	310	400	510	6
8582260	600 E-500	320	500	615	6
8582340	600 E-600	330	600	765	6
8582420	600 E-800	350	800	1000	6
8582500	600 E-1000	360	1000	1215	6
8582690	600 E-1500	380	1500	1750	6
8582770	600 E-2000	400	2000	2375	6



### E 600 Spare handle ROTBAND-PLUS

Ash or hickory, with hardened steel sleeve, tapered collar, fixing plate and wood screw. With this standard wooden handle, according to DIN 5111, it is possible to convert even ordinary hammer heads, as long as they are to DIN standards, to a ROTBAND-PLUS-hammer.

Method: Hammer the handle into the hammer head until it reaches the casing. Drive the tapered collar into the centre of the handle. Fasten the safety plate with a wood screw.

Code	No.	L mm	🔧	PU
8589190	E 600 E-200	280	55	10
8589270	E 600 E-300	300	110	10
8589350	E 600 E-400	310	120	10
8589430	E 600 E-500	320	125	10
8589510	E 600 E 600	330	130	10
8589780	E 600 E-800	350	170	10
8589860	E 600 E-1000	360	235	10
8589940	E 600 E-1500	380	255	10
8593700	E 600 E-2000	400	345	10

DIN 5111

