

FEATURES

- Die cast aluminum gear housing
- Optimal cooling by axial/radial fan
- Two-speed gear unit
- Powerful impact mechanism
- Robust Metabo Marathon motor
- Metabo S-automatic torque limiting clutch
- Metabo winding protection grid
- Spindle with hexagon recess for screwdriver bits



SB 660

SBE 660

	660 Watt Two-Speed Impact Drill SB 660	660 Watt Electronic Two-Speed Impact Drill SBE 660
Special advantages		
■ Variospeed (V) electronics		•
■ Thumbwheel for preselection of speed		•
■ Forward and reverse running		•
■ Geared chuck	•	
■ Futuro Top keyless chuck		•
■ Rubber-coated handle		•
Comparable specifications		
Torque	16 Nm/6 Nm	16 Nm/6 Nm
Drill diameter in		
- Concrete	16 mm	16 mm
- Steel	13 mm/8 mm	13 mm/8 mm
- Softwood	30 mm/20 mm	30 mm/20 mm
Speeds at no load	1,000/min/3,000/min	0 - 1,000/0 - 3,000/min
Rated input power	660 W	660 W
Output power	380 W	380 W
Speed at rated load	610/min/1,850/min	610/min/1,850/min
Maximum impact rate	57,000/min	57,000/min
Collar diameter	43 mm	43 mm
Spindle thread	1/2" - 20 UNF	1/2" - 20 UNF
Chuck capacity	1,5 - 13 mm	1 - 13 mm
Spindle with hexagon recess		1/4" (6.35 mm)
Weight (excluding mains lead)	2.1 kg	2.1 kg
Standard equipment	Geared chuck, drill chuck key, additional handle, drill depth-stop, plastic case	Futuro Top keyless chuck, additional handle, drill depth-stop, plastic case
Type	SB 660	SBE 660
Order no.	6.00660.50 ■	6.00661.50 ■