


# GaAlAs Infrared Emitting Diodes

T-1<sup>3</sup>/<sub>4</sub> (5 mm) Bullet Package — 880 nm

# VTE1285H



## PACKAGE DIMENSIONS inch (mm)



**1** Plastic contour not controlled in region of the leads.

## DESCRIPTION

CASE 62 T-1<sup>3</sup>/<sub>4</sub> (5 mm) BULLET  
CHIP SIZE: .015" x .015"

This 5 mm diameter, custom lensed device contains a medium area, single wirebonded, GaAlAs, 880 nm high efficiency IRED chip. The custom lens allows this cost effective device to have a very narrow half power beam emission of  $\pm 8^\circ$ .

## RoHS Compliant



## ABSOLUTE MAXIMUM RATINGS @ 25°C (unless otherwise noted) ■

Maximum Temperatures									
Storage and Operating:	-40°C to 100°C	Maximum Reverse Voltage:	5.0V						
Continuous Power Dissipation:	200 mW	Maximum Reverse Current @ $V_R = 5V$ :	10 $\mu A$						
Derate above 30°C:	2.86 mW/°C	Peak Wavelength (Typical):	880 nm						
Maximum Continuous Current:	100 mA	Junction Capacitance @ 0V, 1 MHz (Typ.):	23 pF						
Derate above 30°C:	1.43 mA/°C	Response Time @ $I_F = 20$ mA							
Peak Forward Current, 10 $\mu s$ , 100 pps:	2.5 A	Rise: 1.0 $\mu s$ Fall: 1.0 $\mu s$							
Temp. Coefficient of Power Output (Typ.):	-8%/°C	Lead Soldering Temperature:	260°C						
		(1.6 mm from case, 5 seconds max.)							

## ELECTRO-OPTICAL CHARACTERISTICS @ 25°C (See also GaAlAs curves, pages 108-110)

Part Number ■	Output						Forward Drop		Half Power Beam Angle	
	Irradiance		Radiant Intensity	Total Power	Test Current	$V_F$				
	$E_e$		Condition		$I_e$	$P_O$	$I_{FT}$	@ $I_{FT}$	$\theta_{1/2}$	
	mW/cm <sup>2</sup>		distance	Diameter	mW/sr	mW	mA (Pulsed)	Volts		Typ.
	Min.	Typ.	mm	mm	Min.	Typ.		Typ.	Max.	
VTE1285H	3.0	5.5	36	6.4	39	20	100	1.5	2.0	$\pm 8^\circ$

■ Refer to General Product Notes, page 2.