


Schottky Barrier Rectifiers



Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. The proprietary barrier technology allows for reliable operation up to 175°C junction temperature. Typical application are in switching mode power supplies such as adaptors, DC/DC converters, free-wheeling and polarity protection diodes.


Switch mode Full Plastic Dual Schottky Barrier Power Rectifiers



Features:


- Low forward voltage.
- Low switching noise.
- High current capacity.
- Guarantee reverse avalanche.
- Guard-ring for stress protection.
- Low power loss and high efficiency.
- 175°C operating junction temperature.
- Low stored charge majority carrier conduction.
- Plastic material used carries Underwriters Laboratory Flammability Classification 94V-O

20 Amperes
200 Volts
ITO-220AB



Dimensions : Millimetres

DIM	MILLIMETERS	
	MIN	MAX
A	15.05	15.15
B	13.35	13.45
C	10.00	10.10
D	6.55	6.65
E	2.65	2.75
F	1.55	1.65
G	1.15	1.25
H	0.55	0.65
I	2.50	2.60
J	3.00	3.20
K	1.10	1.20
L	0.55	0.65
M	4.40	4.60
N	1.15	1.25
O	3.35	3.45
P	2.65	2.75
Q	3.15	3.25



Common Cathode

Part Number Table

Description	Part Number
Schottky Barrier Rectifiers	MBRF20200CT

Mechanical Data:

Case : JEDEC ITO-220AB moulded plastic body.
 Terminals : Plated lead, solderable per MIL-STD-750, method 2026.
 Maximum mounting Torque : 5 in-lbs.
 Weight : 1.7g approximately.

Maximum Ratings

Characteristic	Symbol	MBRF20200C	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V_{RRM} V_{RWM} V_R	200	V
RMS Reverse Voltage	$V_{R(RMS)}$	140	
Average Rectifier Forward Current Total Device (Rated V_R), $T_C = 125^\circ\text{C}$	$I_{F(AV)}$	10 20	
Peak Repetitive Forward Current (Rate V_R , Square Wave, 20kHz)	I_{FM}	20	A
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions half-wave, single phase, 60Hz)	I_{FSM}	150	
Operating and Storage Junction Temperature Range	T_J, T_{STG}	-65 to +175	$^\circ\text{C}$

Thermal Resistances

Typical Thermal Resistance junction to case	$R_{\theta jc}$	3.8	$^\circ\text{C/W}$
---	-----------------	-----	--------------------


Electrical Characteristics

Characteristic	Symbol	MBRF20200C	Units
Maximum Instantaneous Forward Voltage ($I_F = 10$ Amperes $T_C = 25^\circ\text{C}$) ($I_F = 10$ Amperes $T_C = 125^\circ\text{C}$)	V_F	0.95 0.85	V
Maximum Instantaneous Reverse Current (Rated DC Voltage, $T_C = 25^\circ\text{C}$) (Rated DC Voltage, $T_C = 125^\circ\text{C}$)	I_R	0.01 10	mA


Schottky Barrier Rectifiers




Forward Current Derating Curve




Typical Forward Characteristics



Typical Reverse Characteristics



Typical Junction Capacitance



Peak Forward Surge Current

