



The 50/EF with quick-action chuck. Practical for use with different shaft diameters!



MICROMOT 50/EF



Slim, easily handled and light.

Quick-action chuck and electronic revolutions adjustment, with feedback effect (high engine power in the lower revolutions area). Special, balanced, low noise DC motor with high life expectancy. A transformer is required for operation. We recommend MICROMOT mains adapters from 1.0A.

Technical data:

Direct voltage 12 - 18V. Power consumption max. 40W. Stroke speed 5,000 - 20,000rpm. Length 220mm. Weight 230g.

NO 28 512

**Note:**

The MICROMOT 50/EF can also be fitted with MICROMOT steel collets. This is recommended when milling continuously at high lateral pressure. This makes it impossible for the shafts to become loosened after prolonged working. Using collets makes true running better than using the quick-action chuck.

Other interesting machines and suitable accessories:

[Mill/drill units MICROMOT 50 and MICROMOT 50/E](#)

[MICROMOT mains adapters NG 2/S and NG 2/E](#)

[MICROMOT mains adapter NG 5/E](#)

[Footswitch FS](#)

[Angle adapter WS 90](#)

- ❶ Quick-action chuck of 0.3 - 3.2mm. Primarily advantageous when working with DIN 338 HSS drills of different shank sizes.
- ❷ 20mm standard collar for conveniently fitting MICROMOT-system accessories.
- ❸ Stable housing of glass-fibre reinforced POLYAMIDE. With pleasant soft component in finger grip area.