

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 7443551130


Bezeichnung : SPEICHERDROSSEL WE-HCI

description : POWER-CHOKE WE-HCI



DATUM / DATE : 2009-12-11

A Mechanische Abmessungen / dimensions:




A	13,2 ± 1,0	mm
B	12,8 ± 0,5	mm
C	6,2 ± 0,3	mm
D	2,5 +1,0 / -0,5	mm
E	6,0 ± 0,5	mm
F	6,4 ± 0,5	mm
G	3,0 ± 1,0	mm

Marking = part number

B Elektrische Eigenschaften / electrical properties:

Eigenschaften / properties	Testbedingungen / test conditions		Wert / value	Einheit / unit	tol.
Lerrlaufinduktivität / initial inductance	100 kHz / 0,1V	L ₀	1,30	μH	± 20%
Nenn-Induktivität / rated inductance	100 kHz / 0,1V / 25A	L _N	0,90	μH	typ.
DC-Widerstand / DC-resistance	@ 20° C	R _{DC}	1,80	mΩ	± 10%
Nennstrom / rated current	ΔT= 50 K	I _N	25,0	A	typ.
Sättigungsstrom / saturation current	ΔL/L ₀ = 30 %	I _{sat}	25,0	A	typ.
Eigenres.-Frequenz / self-res.-frequency		SRF	59,0	MHz	typ.

C Lötpad / soldering spec.:



D Prüfgeräte / test equipment:

WAYNE KERR 3260B für/for L₀; I_{SAT}

HP 34401 A & Fluke 54II für/for I_{DC};

Metra HIT 27I für/for R_{DC}

E Testbedingungen / test conditions:

Luftfeuchtigkeit / humidity:	33%
Umgebungstemperatur / temperature:	+20°C

F Werkstoffe & Zulassungen / material & approvals:

Basismaterial / base material:	WE-Perm
Draht / wire:	AIW-100; Class H(200°)

G Eigenschaften / general specifications:

Arbeitstemperatur / operating temperature:	-40°C - +155°C
Umgebungstemp. / ambient temperature:	-40°C - +105°C
It is recommended that the temperature of the part does not exceed 155°C under worst case operating conditions.	

Freigabe erteilt / general release:

Kunde / customer

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

BD	Version 5	09-12-11
ME	Version 4	08-01-01
ME	Version 3	05-04-16
ME	Version 2	05-03-30
ME	Version 1	05-03-17
Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
http://www.we-online.de

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 7443551130

LF




Bezeichnung : **SPEICHERDROSSEL WE-HCI**

description : **POWER-CHOKE WE-HCI**

WÜRTH ELEKTRONIK

DATUM / DATE : 2009-12-11

H Induktivitätskurve / Inductance curve:



Freigabe erteilt / general release:	Kunde / customer				
			BD	Version 5	09-12-11
Datum / date		Unterschrift / signature	ME	Version 4	08-01-01
	Würth Elektronik		ME	Version 3	05-04-16
			ME	Version 2	05-03-30
			ME	Version 1	05-03-17
Geprüft / checked		Kontrolliert / approved	Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
http://www.we-online.de

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 7443551130

LF




Bezeichnung : **SPEICHERDROSSEL WE-HCI**

description : **POWER-CHOKE WE-HCI**

WÜRTH ELEKTRONIK

DATUM / DATE : 2009-12-11

I Temperaturanstieg / Temperature rise curve:



Freigabe erteilt / general release:	Kunde / customer				
Datum / date		Unterschrift / signature		BD	Version 5
				ME	Version 4
				ME	Version 3
				ME	Version 2
				ME	Version 1
Geprüft / checked		Kontrolliert / approved		Name	Änderung / modification
				Datum / date	

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.de>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 7443551130

LF





Bezeichnung : **SPEICHERDROSSEL WE-HCI**

description : **POWER-CHOKE WE-HCI**

WÜRTH ELEKTRONIK

DATUM / DATE : 2009-12-11

I Rollenspezifikation / tape and reel specification:




Gurtspezifikation / Tape specification:

A	14,0 ± 0,1	mm
B	16,0 ± 0,1	mm
C	1,50 ± 0,1	mm
D	1,50 ± 0,1	mm
E	4,00 ± 0,1	mm
F	2,00 ± 0,1	mm
G	1,75 ± 0,1	mm
H	11,5 ± 0,1	mm
I	13,6 ± 0,1	mm
J	6,80 ± 0,1	mm
T	0,40 ± 0,05	mm
W	24,0 ± 0,3	mm

Rollenspezifikation / Reel specification:

a	330,0 ± 2,0	mm
b	24,5 ± 0,8	mm
c	29,5 ± 0,5	mm
d	100,0 ± 1,5	mm



The Force for tearing off cover tape is 20 to 70 grams in arrow direction

Freigabe erteilt / general release:

Kunde / customer

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

ME	Version 4	08-01-01
ME	Version 3	05-04-16
ME	Version 2	05-03-30
ME	Version 1	05-03-17
Name	Änderung / modification	Datum / date

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc, Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400

<http://www.we-online.com>