


High Speed Infrared Emitting Diodes, 850 nm, Surface Emitter Technology



DESCRIPTION

VSMY2850 series are infrared, 850 nm emitting diodes based on GaAlAs surface emitter chip technology with extreme high radiant intensities, high optical power and high speed, molded in clear, untinted plastic packages (with lens) for surface mounting (SMD).

FEATURES

- Package type: surface mount
- Package form: GW, RGW
- Dimensions (L x W x H in mm): 2.3 x 2.3 x 2.8
- Peak wavelength: $\lambda_p = 850$ nm
- High reliability
- High radiant power
- Very high radiant intensity
- Angle of half intensity: $\phi = \pm 10^\circ$
- Suitable for high pulse current operation
- Terminal configurations: gullwing or reserve gullwing
- Package matches with detector VEMD2500X01 series
- Floor life: 4 weeks, MSL 2a, acc. J-STD-020
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



APPLICATIONS

- IrDA compatible data transmission
- Miniature light barrier
- Photointerrupters
- Optical switch
- Emitter source for proximity sensors
- IR touch panels
- IR illumination

PRODUCT SUMMARY

COMPONENT	I_e (mW/sr)	ϕ (deg)	λ_p (nm)	t_r (ns)
VSMY2850RG	100	± 10	850	10
VSMY2850G	100	± 10	850	10

Note

- Test conditions see table "Basic Characteristics"

ORDERING INFORMATION

ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM
VSMY2850RG	Tape and reel	MOQ: 6000 pcs, 6000 pcs/reel	Reverse gullwing
VSMY2850G	Tape and reel	MOQ: 6000 pcs, 6000 pcs/reel	Gullwing

Note

- MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V_R	5	V
Forward current		I_F	100	mA
Peak forward current	$t_p/T = 0.5$, $t_p = 100\ \mu\text{s}$	I_{FM}	200	mA
Surge forward current	$t_p = 100\ \mu\text{s}$	I_{FSM}	1	A
Power dissipation		P_V	190	mW
Junction temperature		T_j	100	$^{\circ}\text{C}$
Operating temperature range		T_{amb}	- 40 to + 85	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	- 40 to + 100	$^{\circ}\text{C}$
Soldering temperature	acc. figure 7, J-STD-020	T_{sd}	260	$^{\circ}\text{C}$
Thermal resistance junction/ambient	J-STD-051, soldered on PCB	R_{thJA}	250	K/W




Fig. 1 - Power Dissipation Limit vs. Ambient Temperature




Fig. 2 - Forward Current Limit vs. Ambient Temperature

BASIC CHARACTERISTICS ($T_{amb} = 25^{\circ}\text{C}$, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	$I_F = 100\ \text{mA}$, $t_p = 20\ \text{ms}$	V_F		1.65	1.9	V
	$I_F = 1\ \text{A}$, $t_p = 100\ \mu\text{s}$	V_F		2.9		V
Temperature coefficient of V_F	$I_F = 1\ \text{mA}$	TK_{VF}		- 1.45		mV/K
	$I_F = 10\ \text{mA}$	TK_{VF}		- 1.3		mV/K
Reverse current		I_R	not designed for reverse operation			μA
Junction capacitance	$V_R = 0\ \text{V}$, $f = 1\ \text{MHz}$, $E = 0\ \text{mW/cm}^2$	C_J		125		pF
Radiant intensity	$I_F = 100\ \text{mA}$, $t_p = 20\ \text{ms}$	I_e	50	100	150	mW/sr
	$I_F = 1\ \text{A}$, $t_p = 100\ \mu\text{s}$	I_e		850		mW/sr
Radiant power	$I_F = 100\ \text{mA}$, $t_p = 20\ \text{ms}$	ϕ_e		55		mW
Temperature coefficient of radiant power	$I_F = 100\ \text{mA}$	$TK\phi_e$		- 0.35		%/K
Angle of half intensity		ϕ		± 10		deg
Peak wavelength	$I_F = 100\ \text{mA}$	λ_p	840	850	870	nm
Spectral bandwidth	$I_F = 30\ \text{mA}$	$\Delta\lambda$		30		nm
Temperature coefficient of λ_p	$I_F = 30\ \text{mA}$	$TK\lambda_p$		0.25		nm/K
Rise time	$I_F = 100\ \text{mA}$, 20 % to 80 %	t_r		10		ns
Fall time	$I_F = 100\ \text{mA}$, 20 % to 80 %	t_f		10		ns
Virtual source diameter		d		1.5		mm

BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 3 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Radiant Power vs. Wavelength




Fig. 4 - Radiant Intensity vs. Forward Current




Fig. 6 - Relative Radiant Intensity vs. Angular Displacement

SOLDER PROFILE




Fig. 7 - Lead (Pb)-free Reflow Solder Profile acc. J-STD-020

DRYPACK

Devices are packed in moisture barrier bags (MBB) to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

FLOOR LIFE

Floor life (time between soldering and removing from MBB) must not exceed the time indicated on MBB label:

Floor life: 4 weeks


Conditions: $T_{amb} < 30\text{ }^{\circ}\text{C}$, RH < 60 %

Moisture sensitivity level 2a, acc. to J-STD-020.


DRYING

In case of moisture absorption devices should be baked before soldering. Conditions see J-STD-020 or label. Devices taped on reel dry using recommended conditions 192 h at 40°C (+ 5°C), RH < 5 %.

Vishay Semiconductors High Speed Infrared Emitting Diodes,
850 nm, Surface Emitter Technology



Not indicated tolerances ± 0.1



www.vishay.com
4

For technical questions, contact: emittertechsupport@vishay.com







Document Number: 83398
Rev. 1.0, 22-Dec-10



VSMY2850RG, VSMY2850G


High Speed Infrared Emitting Diodes, Vishay Semiconductors
850 nm, Surface Emitter Technology

PACKAGE DIMENSIONS in millimeters: VSMY2850G



technical drawings
according to DIN
specifications

Not indicated tolerances ± 0.1




Drawing-No.: 6.544-5383.03-4
Issue: 1; 18.03.10
22099

VSMY2850RG, VSMY2850G




Vishay Semiconductors High Speed Infrared Emitting Diodes,
850 nm, Surface Emitter Technology

TAPING AND REEL DIMENSIONS in millimeters: VSMY2850RG




Leader and trailer tape:




Terminal position in tape

Device	Lead I	Lead II
VEMT2000	Collector	Emitter
VEMT2500		
VEMD2000	Cathode	Anode
VEMD2500		
VSMB2000		
VSMG2000	Anode	Cathode
VSMY2850RG		




Drawing-No.: 9.800-5100.01-4
Issue: 2; 18.03.10
21572

TAPING AND REEL DIMENSIONS in millimeters: **VSMY2850G**




Leader and trailer tape:



Terminal position in tape

Devicce	Lead I	Lead II
VENT2020	Collector	Emitter
VENT2520		
VSMB2020	Cathode	Anode
VSMG2020		
VEMD2020		
VEMD2520		
VSMT2850G	Anode	Cathode



Drawing-No.: 9.800-5091.01-4

Issue: 3; 18.03.09

21571



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.