





## Five Module

### 4 channel, electronic time switch

Dimensions



Electrical Connections



Mounting



#### Features

Weekly 4-channel switch intended for the control of heating, lighting, watering systems and access control installation etc.

- Very simple programming by selection button - time setting
- programming
- automatic operation
- override

- Days selected by dedicated buttons - one per day
- Manual ON or OFF control for each channel
- Sealable cover
- Connection by cage terminals
- 4 voltage - free 16A change over contacts

#### Functional characteristics

- Possibility to select 84 ON or OFF programming steps per day (up to 588 switchings per week), each defined by: Channel, day(s), time and switching state.

- Programming in steps of 1 minute
- ON or OFF timed override from 1 hour to 99 days
- Power reserve by lithium battery: total of 5 years minimum reserve
- Simultaneous switching off of the 4 channels by means of an external contact connected to the mains live

#### Technical characteristics

Supply voltage	220/240 V
Frequency	50/60 Hz
Power consumption	approx. 20 VA
Changeover contacts	resistive load 16 A 250 V
resistive load	inductive load ( $\cos \phi = 0.6$ ) 3 A 250 V
Accuracy of operation	1 sec / 24 h.
Operating temperature	-10 °C to +50 °C
Storage temperature	-20 °C to +60 °C
Connection by cage terminals, section of conductors	1.5 to 4 mm <sup>2</sup>
Conformity to standard BS EN 60730	yes

Performance indicated for an ambient temperature of 20 °C

Reference	Cycle	Voltage free changeover contacts
27403	7 day	4 x 16 (3) A

Reference	Accessories
143541	Enclosure

Sangamo Limited  
Industrial Estate, Port Glasgow, Renfrewshire, PA14 5XG  
Tel: 0845 006 6206 Fax: 01475 744567  
Email : [enquiries@sangamo.co.uk](mailto:enquiries@sangamo.co.uk) Web: [www.sangamo.co.uk](http://www.sangamo.co.uk)

Data Sheet: DS0004\_A