NETGEAR®
Connect with Innovation™

N600 Wireless Dual Band Router
WNDR3400

High Performance

| SPEED 300+300 | SECURE CONNECTION | WI-FI AND POWER ON/OFF BUTTONS | PARENTAL CONTROLS | BEST RANGE | MULTIPLAYER GAMING | USB STORAGE ACCESS | STREAMING MULTIMEDIA | DUAL BAND |

CHOOSE THE ROUTER THAT'S RIGHT FOR YOU

Product	Speed	Range	Surf, email, and chat	Wireless printing	Simultaneous downloads, voice, and music	Online gaming	Larger home or multiple floors	HD video streaming	Avoids interference
Simple Sharing N150	Up to 150 Mbps[†]	Good	✓	✓					
Work and Play N300	Up to 300 Mbps[†]	Better	✓	✓	✓	✓			
High Performance N600	Up to 300 + 300 Mbps[†]	Best	✓	✓	✓	✓	✓	✓	✓

Dual Band avoids interference

Faster downloads and Internet gaming

ReadySHARE™— share USB storage

Faster multimedia streaming

THE NETGEAR DIFFERENCE - WNDR3400

- ✓ ReadySHARE USB Storage Access
- ✓ Live Parental Controls – Free!
- ✓ Simultaneous Dual Band Wireless-N
- ✓ Broadband usage meter
- ✓ Guest network access

ReadySHARE USB STORAGE ACCESS

- ✓ Connect your USB storage device to your network
- ✓ Easily share multimedia and data files
- ✓ Fast read/write speeds for large files

ReadySHARE™ USB

PRODUCT OVERVIEW

The NETGEAR N600 Wireless Dual Band Router offers the high-performance wireless Internet access needed for demanding applications, such as streaming multimedia and multiplayer gaming. Dual band technology avoids interference, ensuring top speeds and the greatest range.

- **Dual band** — Offers twice the bandwidth with better connection and less interference
- **Faster multimedia streaming** — Provides Wireless-N speed and dual band performance for streaming video, multiplayer online gaming and simultaneous downloads
- **Shared storage** — ReadySHARE™ provides fast and easy shared access to an external USB storage device
- **Jitter-free video and gaming** — Video Quality of Service (QoS) for reliable Internet connections
- **Live Parental Controls** — keeps your Internet experience safe
  – Blocks unsafe Internet content and applications and can be managed from anywhere
  – Protects connected devices through the router such as PCs, gaming consoles, and iPod touch®
  – To learn more visit www.netgear.com/lpc
- **Guest network access** — Provides separate security and access restrictions for guests using the network
- **Broadband usage meter** — ensures daily, weekly and monthly measurement of Internet traffic with customized alerts
- **Easy setup** — Smart Wizard® CD with graphical installation guide
- **Secured connection** — Push 'N' Connect with Wi-Fi Protected Setup® (WPS)[1] ensure a quick and secure network connection
- **NETGEAR Green features** — Power and Wi-Fi on/off buttons, Energy Star-compliant power adapter and 80% recycled packaging

Notebooks and Desktop PCs
connect with N300 Wireless Adapters

Connects
to power

Power
on/off
button

Connect to
desktop PCs
and notebooks

Connects to
cable/DSL
modem

Wi-Fi
on/off
button

ReadySHARE USB
Storage Access
(connects to external,
flash, or pen drives)

Package Contents

- N600 Wireless Dual Band Router (WNDR3400)
- Stand
- Ethernet cable
- Smart Wizard® installation CD
- Power adapter, localized to country of sale

Warranty

- Localized to country of sale

System Requirements

- Broadband (cable, DSL) Internet service and modem with Ethernet connection
- 2.4 or 5.0 GHz 802.11a/b/g/n specification wireless adapter or an Ethernet adapter and cable for each computer
- Microsoft® Windows® 7, Vista®, XP, 2000, Mac OS®, UNIX®, or Linux®
- Microsoft® Internet Explorer® 5.0, Firefox® 2.0 or Safari 1.4 or higher

Standards

- IEEE® 802.11 b/g/n 2.4 GHz
- IEEE 802.11 a/n 5.0 GHz
- Five (5) 10/100 (1 WAN and 4 LAN) Ethernet ports with auto-sensing technology

Performance

- 480 MHz powerful MIPS 32-bit processor
- Memory: 8 MB flash and 64 MB RAM
- Five (5) (1 WAN, 4 LAN) Fast Ethernet ports
- Advanced Quality of Service (QoS)
- Supports Wireless Multimedia (WMM) based QoS

Security

- Wi-Fi Protected Access® (WPA/WPA2—PSK) and WEP
- Double firewall protection (SPI and NAT firewall)
- Denial-of-service (DoS) attack prevention

Ease of Use

- Smart Wizard® installation CD
- Push 'N' Connect using Wi-Fi Protected Setup® (WPS)[1]

Physical Specifications

- Dimensions: 223 x 153 x 31 mm (8.8 x 6.0 x 1.2 in)
- Weight: 0.5 kg (1.2 lb)

Advanced Features

- Live Parental Controls with flexible and customizable filter settings
- Simultaneous Dual Band—2.4 GHz and 5 GHz operation
- ReadySHARE™ USB storage access—supports FAT16/32, NTFS Read/Write
- Multiple SSID guest networks (separate security and access restrictions)
- Broadband usage meter measures Internet usage
- Power and Wi-Fi on/off buttons

NETGEAR Green Features

- Power On/Off Button
- 80% Recycled Packaging
- CEC (California Efficiency)
- RoHS
- WEEE
- Wireless On/Off Button
- Energy Star Compliant Power Adapter

Compatible with
Windows®7

Mac

a b g Wi-Fi n
CERTIFIED®

Wi-Fi PROTECTED
SETUP

ENERGY STAR

Powered by an
ENERGY STAR®
qualified adapter
for a better
environment

NETGEAR
Green™

D-WNDR3400-1