

POWERSAVER Range



Product: PSB

The Powersaver Boost is a simple to use, multi application time switch. Although primarily used for the control of water heating, the PSB can also be used for a multitude of applications including the control of panel heaters, security lighting or combi boilers.

Electronic Boost controller with a single button operation, offering three user-selectable boost periods of 1/2 hour, 1 hour or 2 hours. An indicator light on the product shows the remaining time.

One of the main benefits of the Powersaver Boost product is its standard size. This is common to all models, which fit directly onto a single gang patress box. This allows installation or upgrading from one model to another, quick and simple.

The Powersaver family saves on fuel expenditure and energy wastage by automatically switching off when the user may forget.

Product Specification

Contact Rating 16A Resistive 240V a.c.

Supply 230V 50/60 Hz a.c.

Fixing Single Patress - Surface and Flush Mounting

Resolution of Programs N/A

Power Consumption 10VA Maximum

Live Parts Protection This unit is totally protected by the enclosure

Dirt and Moisture Protection IP00

Shock Protection Class 1 (this unit must be connected to earth)

Case Material Polycarbonate

Type of Action Type 1B

Temperature Rating T35

Operation Temperature 0°C to 35°C

Memory Reserve none

Display none

Program Settings none

Boost Settings User selectable - 1/2, 1 or 2 hours

Control Pollution Category Normal

 switched on solutions


SANGAMO

Sales Office Direct Line : 0845 006 6206 Fax: 01475 744567 Email: enquiries@sangamo.co.uk

POWERSAVER Range

Product: PSB

Wiring Diagram



Dimensions

