



HiPerFRED

High Performance Fast Recove
Low Loss and Soft Recovery
Common Cathode

Part number

DPG 30 C 400 HB



Backside: cathode

Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm}-values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package:


- Housing: TO-247
- Industry standard outline
- Epoxy meets UL 94V-0
- RoHS compliant

Ratings

Symbol	Definition	Conditions	Ratings			Unit	
			min.	typ.	max.		
V _{RRM}	max. repetitive reverse voltage				400	V	
I _R	reverse current	V _R = 400V			1	μA	
		V _R = 400V			0.1	mA	
V _F	forward voltage	I _F = 15A			1.39	V	
		I _F = 30A			1.58	V	
		I _F = 15A	T _{VJ} = 150°C			1.07	V
			I _F = 30A			1.27	V
I _{FAV}	average forward current	rectangular, d = 0.5			15	A	
V _{F0}	threshold voltage	} for power loss calculation only			0.75	V	
r _F	slope resistance				18.7	mΩ	
R _{thJC}	thermal resistance junction to case				1.70	K/W	
T _{VJ}	virtual junction temperature		-55		175	°C	
P _{tot}	total power dissipation				90	W	
I _{FSM}	max. forward surge current	t = 10 ms (50 Hz), sine			150	A	
I _{RM}	max. reverse recovery current				4	A	
		I _F = 10 A			tbd	A	
		-di _F /dt = 200 A					
t _{rr}	reverse recovery time	V _R = 100 V	T _{VJ} = 25°C		45	ns	
			T _{VJ} = 125°C		tbd	ns	
C _J	junction capacitance	V _R = 200 V; f = 1 MHz			15	pF	

Symbol	Definition	Conditions	Ratings			Unit
			min.	typ.	max.	
I_{RMS}	RMS current	per pin ¹⁾			35	A
R_{thCH}	thermal resistance case to heatsink			0.25		K/W
T_{stg}	storage temperature		-55		150	°C
Weight				6		g
M_D	mounting torque		0.8		1.2	Nm
F_C	mounting force with clip		20		120	N

¹⁾ I_{RMS} is typically limited by: 1. pin-to-chip resistance; or by 2. current capability of the chip.
 In case of 1, a common cathode/anode configuration and a non-isolated backside, the whole current capability can be used by connecting the backside.


Product Marking

Part number

D = Diode
 P = HiPerFRED
 G = extreme fast
 30 = Current Rating [A]
 C = Common Cathode
 400 = Reverse Voltage [V]
 HB = TO-247AD (3)

Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Code Key
Standard	DPG 30 C 400 HB	DPG30C400HB	Tube	30	505790

Similar Part	Package	Voltage Class
DPG30C400PB	TO-220	400

Outlines TO-247



Symbol	Inches		Millimeters	
	min	max	min	max
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215 BSC		5.46 BSC	
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
$\varnothing P$	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242 BSC		6.14 BSC	
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
$\varnothing P1$	-	0.291	-	7.39

