


Data Sheet

Chip Monolithic Ceramic Capacitors

Medium Voltage Large Capacitance and High Allowable Ripple Current

GR355DD72W224KW01L (2220, X7T, 0.22μF, DC450V)

RoHS regulation conformity parts



■ Dimensions

Length L	5.7mm±0.4mm
Width W	5.0mm±0.4mm
Thickness T	2.0mm+0/-0.3mm
Electrode e	0.3mm min.
Electrode g (min.)	3.2mm

■ Rated Value

	Murata PN Code	Spec
Temperature Char.	D7	X7T(EIA), +22/-33%
Capacitance	224	0.22μF
Capacitance Tol.	K	±10%
Rated Voltage	2W	DC450V

■ Packaging

Code	Packaging	Minimum Quantity
L	180mm Embossed Tape	1000

■ Specifications

Please refer to
'Medium Voltage High Effective Capacitance Type
Specifications and Test Methods'
PDF file.

● This data sheet is applied for CHIP MONOLITHIC CERAMIC CAPACITOR used for General Electronics equipment for your design.

<Notice>

- Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.
- Please refer to 'Caution' and 'Notice' for the other details.

- The RoHS compliance means that we judge from EU Directive 2002/95/EC the products do not contain lead, cadmium, mercury, hexavalent chromium, PBB and PBDE, except exemptions stated in EU Directive 2002/95/EC annex and impurities existing in natural world.
- This statement does not insure the compliance of any of the listed parts with any laws or legal imperatives developed by any EU members individually with regards to the RoHS Directive.

⚠ Note:

1. This datasheet is downloaded from the website of Murata Manufacturing co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.