



## Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 4

TEROSTAT-MS 930 Black DK310MVAG0012D5

sds no. : 267026  
V003.1

Revision: 25.05.2010  
printing date: 16.04.2011

### 1. Identification of the substance/preparation and of the company/undertaking

**Trade name:**

TEROSTAT-MS 930 Black DK310MVAG0012D5

**Intended use:**

1-Component sealant

**Company name:**

Henkel Limited  
Technologies House  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (0)1442 278000  
Fax-no.: +44 (0)1442 278071

**E-mail address of person responsible for Safety Data Sheet:**

ua-productsafety.uk@uk.henkel.com

**Emergency information:**

24 Hours Emergency Tel: +44 (0)1442 278497

### 2. Hazards identification

The product is not hazardous within the meaning of the valid (EU) preparation directive.

### 3. Composition / information on ingredients

**General chemical description:**

1-Component moisture-curing adhesive

**Base substances of preparation:**

Silane-modified polyether

**Declaration of ingredients according to (EC) No 1907/2006:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

### 4. First aid measures

**Inhalation:**

Move to fresh air, consult doctor if complaint persists.

**Skin contact:**

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

**5. Fire fighting measures**

**Suitable extinguishing media:**

All common extinguishing agents are suitable.

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

**Special protection equipment for firefighters:**

Wear self-contained breathing apparatus.  
Wear protective equipment.

**Hazardous combustion products:**

carbon oxides.

**6. Accidental release measures**

**Personal precautions:**

Wear protective equipment.  
See advice in chapter 8

**Environmental precautions:**

Do not empty into drains / surface water / ground water.

**Clean-up methods:**

Remove mechanically.  
Dispose of contaminated material as waste according to item 13.

**7. Handling and storage**

**Storage:**

Ensure good ventilation/extraction.  
Store in a cool, frost-free place.  
Storage at 15 to 25°C is recommended.

**8. Exposure controls / personal protection**

**Components with specific control parameters for workplace:**

Valid for  
Great Britain  
Basis  
UK EH40 WELs

Ingredient	ppm	mg/m3	Type	Category	Remarks
DIISONONYL PHTHALATE 28553-12-0		5	Time Weighted Average (TWA).		EH40 WEL

**Engineering controls:**

Ensure good ventilation/extraction.

**Respiratory protection:**

Suitable breathing mask when there is inadequate ventilation.

**Hand protection:**

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq 1$  mm thickness) or natural rubber (NR;  $\geq 1$  mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq 1$  mm thickness) or natural rubber (NR;  $\geq 1$  mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Protective goggles

**Skin protection:**

Wear protective equipment.

**General protection and hygiene measures:**

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

## 9. Physical and chemical properties

**General characteristics:**

Appearance	solid material pasty Black
Odor:	Characteristic

**Phys./chem. properties:**

Flash point	not applicable
Density (20 °C (68 °F))	1,50 g/cm <sup>3</sup>
Viscosity (dynamic) (; 20 °C (68 °F); Conc.: 100 % product)	120 - 210 pa.s
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Solid content (105 °C )	98 %
VOC content (VOCV 814.018 VOC regulation CH)	0 %

## 10. Stability and reactivity

**Conditions to avoid:**

None if used for intended purpose.

**Materials to avoid:**

None if used for intended purpose.

**Hazardous decomposition products:**

No decomposition if used according to specifications.

## 11. Toxicological information

**General toxicological information:**

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

## 12. Ecological information

**General ecological information:**

Do not empty into drains, soil or bodies of water.

## 13. Disposal considerations

**Product disposal:**

The valid EEC waste code numbers are not product-related but are largely source-related. These can be requested from the manufacturer.

In consultation with the responsible local authority, must be subjected to special treatment.

## 14. Transport information

**General information:**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

## 15. Regulations - classification and identification

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

**VOC Paints and Varnishes (EU):**

Product (sub)category:

This product is not a subject of the Directive 2004/42/EC

## 16. Other information

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.