

Datasheet - AES 1135



Guard door monitors and Safety control modules for
Emergency Stop applications / Monitoring of
electromechanical and non-contact switchgear / AES 113x



- Monitoring of BNS range magnetic safety sensors
- 1 safety contact, STOP 0
- 2 Signalling outputs

(Minor differences between the printed image and the original product may exist!)

Ordering details

Product type description	AES 1135
Article number	1170036
EAN code	4030661296920

Approval

Approval




Classification

Standards	EN ISO 13849-1, IEC 61508
PL	up d
Control category	up 3
PFH value	1.0 x 10 ⁻⁷ /h
SIL	up 2
Mission time	20 Years

Global Properties

Product name	AES 113x
--------------	----------

Standards	IEC/EN 60204-1, IEC 60947-5-3, EN 954-1, BG-GS-ET-14, BG-GS-ET-20
Compliance with the Directives (Y/N) 	Yes
Climatic stress	EN 60068-2-3, BG-GS-ET-14
Mounting	snaps onto standard DIN rail to EN 60715
Terminal designations	IEC/EN 60947-1
Materials	
- Material of the housings	Plastic, glass-fibre reinforced thermoplastic, ventilated
- Material of the contacts	Ag-Ni, 0,2 µm gold flashed
Weight	155 g
Start conditions	Automatic
Start input (Y/N)	No
Feedback circuit (Y/N)	No
Start-up test (Y/N)	No
Reset after disconnection of supply voltage (Y/N)	Yes
Automatic reset function (Y/N)	Yes
Reset with edge detection (Y/N)	No
Pull-in delay	
- ON delay with automatic start	adjustable 0,1 / 1.0 s
Drop-out delay	
- Drop-out delay in case of emergency stop	< 50 ms

Mechanical data

Connection type	Screw connection
Cable section	
- Min. Cable section	0,25 mm ²
- Max. Cable section	2.5 mm ²
Pre-wired cable	rigid or flexible
Tightening torque for the terminals	0,6 Nm
Detachable terminals (Y/N)	No
Mechanical life	20.000.000 operations
Electrical lifetime	150.000 operations for 230 VAC, 5 A (cos φ = 1)
restistance to shock	30 g / 11 ms
Resistance to vibration To EN 60068-2-6	10...55 Hz, Amplitude 0,35 mm, ± 15 %

Ambient conditions

Ambient temperature	
- Min. environmental temperature	0°C
- Max. environmental temperature	+ 55°C
Storage and transport temperature	
- Min. Storage and transport temperature	- 25°C
- Max. Storage and transport temperature	+ 70°C
Protection class	
- Protection class-Enclosure	IP40
- Protection class-Terminals	IP20
- Protection class-Clearance	IP54
Air clearances and creepage distances To IEC/EN 60664-1	
- Rated impulse withstand voltage U _{imp}	4.8 kV
- Overvoltage category	III To VDE 0110
- Degree of pollution	2 To VDE 0110

Electromagnetic compatibility (EMC)

EMC rating 10 V/m

Electrical data

Rated DC voltage for controls	
- Min. rated DC voltage for controls	20.4 V
- Max. rated DC voltage for controls	27.6 V
Rated AC voltage for controls, 50 Hz	
- Min. rated AC voltage for controls, 50 Hz	-
- Max. rated AC voltage for controls, 50 Hz	-
Rated AC voltage for controls, 60 Hz	
- Min. rated AC voltage for controls, 60 Hz	-
- Max. rated AC voltage for controls, 60 Hz	-
Contact resistance	max. 100 mΩ
Power consumption	< 5 W
Type of actuation	DC
Switch frequency	1 Hz
Rated insulation voltage U_i	250 V
Rated operating voltage U_e	24 VDC \pm 15%
Thermal test current I_{the}	6 A
Operating current I_e	0,2 A
Electronic protection (Y/N)	No

Inputs

Monitored inputs

- Short-circuit recognition (Y/N)	optional
- Wire breakage detection (Y/N)	Yes
- Earth connection detection (Y/N)	Yes
Number of shutters	adjustable 1 piece -> 0 piece
Number of openers	adjustable 1 piece -> 2 piece
Input resistance	approx. 4000 Ω at GND
Input signal "1"	10 ... 30 VDC
Input signal "0"	0 ... 2 VDC
Cable length	1000 m with 0,75 mm ² (for Rated voltage)

Outputs

Stop category	0
Number of safety contacts	1 piece
Number of auxiliary contacts	0 piece
Number of signalling outputs	2 piece
Switching capacity	
- Switching capacity of the safety contacts	min. 10 mA, max. 6 A
- Switching capacity of the signaling/diagnostic outputs	Y1-Y2 = 100 mA
Fuse rating	
- Protection of the safety contacts	6 A gG D-fuse
- Fuse rating for the signaling/diagnostic outputs	short-circuit proof
Signalling output	Y1: Authorized operation, safety contacts on; Y2: No authorised operation, safety contacts off
Utilisation category To EN 60947-5-1	AC-15: 230 V / 3 A DC-13: 24 V / 2 A
Number of undelayed semi-conductor outputs with signaling function	2 piece
Number of undelayed outputs with signaling function (with	

contact)	0 piece
Number of delayed semi-conductor outputs with signaling function.	0 piece
Number of delayed outputs with signalling function (with contact).	0 piece
Number of secure undelayed semi-conductor outputs with signaling function	0 piece
Number of secure, undelayed outputs with signaling function, with contact.	0 piece
Number of secure, delayed semi-conductor outputs with signaling function	0 piece
Number of secure, delayed outputs with signaling function (with contact).	0 piece

LED switching conditions display

LED switching conditions display (Y/N)	Yes
Number of LED's	1 piece

Integral system diagnosis ISD

Integral system diagnosis ISD

- The following faults are registered by the safety monitoring modules and indicated by ISD
- Failure of door contacts to open or close
- Cross-wire or short-circuit monitoring of the switch connections
- Interruption of the switch connections
- Failure of the safety relay to pull-in or drop-out
- Fault on the input circuits or the relay control circuits of the safety monitoring module

Miscellaneous data

Applications



Safety sensor



Guard system

Dimensions

Dimensions

- Width 22.5 mm
- Height 100 mm
- Depth 121 mm

notice

Inductive loads (e.g. contactors, relays, etc.) are to be suppressed by means of a suitable circuit.

notice - Wiring example

To secure a guard door up to PL 3 and Category #03#

Monitoring 1 guard door(s), each with a magnetic safety sensor of the BNS range

If one or two external relays or contactors are used to switch the load, the system can then only be classified in Category 3 to EN 954-1, if exclusion of the fault "Failure of the external contactors" can be substantiated and is documented, e.g. by using reliable down-rated contactors. A second contactor leads to an increase in the level of security by redundant switching to switch the load off.

Modification for 2 NC contacts:

The safety monitoring module can be modified to monitor two NC contacts by bridging the terminals A1 and X1. The short-circuit recognition

between connections then becomes inoperative.

Expansion of enable delay time:

The enable delay time can be increased from 0,1 s to 1,0 s by changing the position of a jumper link connection under the cover of the unit.

The wiring diagram is shown with guard doors closed and in de-energised condition.

The ISD tables (Integral System Diagnostics) for analysis of the fault indications and their causes are shown in the appendix.

Documents

Operating instructions and Declaration of conformity (de) 824 kB, 30.11.2010

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/DE/mrl_aes1135_1136_de.pdf

Operating instructions and Declaration of conformity (fr) 673 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/FR/mrl_aes1135_1136_fr.pdf

Operating instructions and Declaration of conformity (it) 660 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/IT/mrl_aes1135_1136_it.pdf

Operating instructions and Declaration of conformity (es) 659 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/ES/mrl_aes1135_1136_es.pdf

Operating instructions and Declaration of conformity (de) 666 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/DE/mrl_aes1135_1136_de.pdf

Operating instructions and Declaration of conformity (nl) 658 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/NL/mrl_aes1135_1136_nl.pdf

Operating instructions and Declaration of conformity (jp) 1 MB, 30.11.2010

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/JP/mrl_aes1135_1136_jp.pdf

Operating instructions and Declaration of conformity (en) 747 kB, 02.12.2009

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/bedien/EN/mrl_aes1135_1136_en.pdf

Wiring example (99) 17 kB, 22.08.2008

http://127.0.0.1/Bilddata/Si_baust/Aes1135/Schaltun/Maes1101.pdf

Wiring example (99) 18 kB, 22.08.2008

http://127.0.0.1/Bilddata/Si_baust/Aes1135/Schaltun/Maes1102.pdf


ISD tables (Integral System Diagnostics) (en) 35 kB, 29.07.2008

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/ISD/i_ae2p02.pdf


ISD tables (Integral System Diagnostics) (de) 51 kB, 29.07.2008

http://127.0.0.1/Bilddata/Si_baust/Pdf/Aes1135/ISD/i_ae2p01.pdf


Images




AES11XX
 AES12XX
 FwS 17XX



Dimensional drawing (basic component)



Wiring example



Wiring example

