


NEW

High speed transmission, 1mm pitch Small Interface Connector

DH Series



Overview

DH Series is an impedance controlled interface connector for high speed transmission.

1mm contact mating pitch together with a 0.5mm mounting pitch yields a more compact, lower profile, higher density alternate to conventional half pitch interface connectors. 4 different lock styles are available to meet various applications.

Screw Lock Type
(Locked with screwdriver)



Screw Lock Type
(Hand-screw)



One Touch Lock Type
(Metal Button)





One Touch Lock Type
(Plastic Button)





Features

1. Small Design

Mating face area
Approx 50% reduced




Mating pitch: 1.27mm




Mating pitch: 1.0mm

2. Robust design



PCB Retention Force

Through hole mounting for shell and metal fitting increases PCB retention force.



Secure Panel Attachment (optional)
with easy to use hexagon sockets.

Robust design resists
wrenching D-shaped opening.



Plug




M2 screw

Robust & Secure Screw Lock

Tightening torque: 0.06 to 0.07 N·m max

3. Excellent Shielding for EMI Prevention

◆Grounding Structure



4. Wide variation

There are various variations corresponding to the usage.

●Lock variation

Lock type	Cover case	receptacle			
Item	Specification / Part number	Item	Part number		
Screw lock	Screwdriver type DH-**-CV1B Hand-screw type DH-**-CV2B	Connector	DH60-**P / DH80-**P		
		Panel lock	Applicable panel thickness(mm)	Number of washers	Part No.
			1.4 to 1.6	0	DH-LNA
			0.9 to 1.2	1(t=0.4)	DH-LNA-W4
			0.5 to 0.8mm	1(t=0.6)	DH-LNA-W8
			No panel	1(t=0.8)	DH-LNA-W16
One touch lock	Metal button DH-**-CT1B Plastic button DH-**-CT2B	Connector	DH60A-**P / DH80A-**P		

*Screw lock type and One touch lock type does not mate together.

●Common part


Lock type	Plug				No. of pos.	Clamp metal
	Connector					
Item	Specification / Part number					Part No.
Screw lock	IDC type				17	DH-17-CMB(6.3)
	Cable spec.	Outer dia.	Construction	Part No.		
	Twinax cable	0.88 to 0.92	7/0.127	DH30B-***S	27	DH-27-CMB(6.9) DH-27-CMB(7.3)
	Twisted pair cable	0.64 to 0.68	(AWG#28)	DH32B-***S		
	solder type				37	DH-37-CMB(8.8)
	DH40-***S					
One touch lock	(Developing Pin-variation of the above item is under planning. Please consult HRS sales.)				51	DH-51-CMB(9.6)

*The figure in () clamp part number is equal to the cable's outer diameter.

5. High Speed Data Transmission

This data is for reference only. The data can differ due to cable or PCB used in evaluation.

Eye Diagram [CH1-CH2]



Measurement Condition

◆ Pin Assignment



Pair B
G - S - S - G

Pair A
G - S - S - G


G:ground
S:Signal

◆ Measurement Condition

- Measurement Pair:Deferential Pair A
- Cable:Twinax cable
- Input signal voltage:500mV

Pulse Pattern Generator

Oscilloscope



■Specifications

Ratings	Current rating		0.5A			Operating temperature range		-25℃ to +85℃		
	Voltage rating		125 V AC			Storage temperature range		-25℃ to +60℃		
Item	Specification						Conditions			
1.Contact resistance	① 50mΩ max.(signal)						100mA(DC or 1,000Hz)			
2.Insulation resistance	1000MΩ min.						100 V DC			
3.Withstanding voltage	No flashover or insulation breakdown						250 V AC/1minute			
4.Insertion and with drawal forces		17pos.	27pos.	37pos.	51pos.		Measured by applicable connector.			
	Insertion f.	25N max.	30N max.	36N max.	43N max.					
	with drawal f.	2.6N min.	3N min.	3.3N min.	3.8N min.					
5.Durability	① ①Contact resistance:70mΩ max. ②No damage, cracks or parts dislocation.						1000 cycles			
6.Vibration	①No electrical discontinuity of 10μs or longer. ②No damage, cracks or parts dislocation.						Frequency:10 to 50Hz, single amplitude of 0.75mm, 5min/cycle, total 10 cycles.			
7.Shock							Acceleration of 490m/s², 11ms duration, sine half-wave waveform, 3 cycles in each of the 3 axis.			
8.Temperature cycle	① ①Contact resistance:70mΩ max. ②No damage, cracks or parts dislocation.						Temperature: -55℃→+5℃ to +35℃→+85℃→5℃ to+35℃ Time:30→5→30→5(Minutes) 5cycles			
9.Humidity (Steady state)	①Insulation resistance:100MΩmin. ②No damage, cracks or parts dislocation.						96 hours at 40℃ And RH 90% to 95%.			
10.Salt spray test	①Contact resistance:100mΩ max.						5% salt water solution for 48 hours.			

① Excludes wire conductor resistance. *Unless otherwise specified, refer to JIS C 5402

2 Information contained in this catalog represents general requirements for this Series. Contact us for the drawings and specifications for a specific part number shown.

■Materials


Products	Components	Material	Finish	Remarks
Screw lock type receptacle connector (DH60-***P / DH80-***P)	Insulator	Polyamide resin	Black	UL94V-0
	Contacts	Copper alloy	Selective gold plated	—
	Shell	Stainless steel	Tin plated	—
	Metal fitting	Stainless steel	Selective Tin plated	—
One Touch Lock Type Receptacl connector (DH60A-***P / DH80A-***P)	Insulator	Polyamide resin	Black	UL94V-0
	Contacts	Copper alloy	selective gold plated	—
	Shell	Stainless steel	Tin plated	—
	Metal fitting	Brass	Tin plated	—
	Metal grounding post	Steel	Nickel plated	—
Plug connector (DH3*B-***S)	Insulator	Polyamide resin	Black	UL94V-0
	Contacts	Copper alloy	Selective gold plated	—
	Rear insert	PBT resin	Black,Natural	UL94V-0
	Shell	Stainless steel	Nickel plated	—
Screw lock type cover case (DH-**-CV1B)	Cover	Polycarbonate resin	Black	UL94V-0
	Shield	Stainless steel	Nickel plated	—
	Screw lock	Steel	Nickel plated	—
	Tapping screw	Steel	Black chromate(Cr+3)	—
Lock type cover case (DH-**-CV2B)	Cover	Polycarbonate resin	Black	UL94V-0
	Shield	Stainless steel	Nickel plated	—
	Screw lock	Steel	Nickel plated	—
	Screw insulator	Polyamide resin	Black	UL94V-0
	Tapping screw	Steel	Black chromate(Cr+3)	—
One Touch Lock Type metal button cover case (DH-**-CT1B)	Cover	Polycarbonate resin	Black	UL94V-0
	Shield	Stainless steel	Nickel plated	—
	Lock spring	Stainless steel	—	—
	Tapping screw	Steel	Black chromate(Cr+3)	—
One Touch Lock Type plastic button cover case (DH-**-CT2B)	Cover	Polycarbonate resin	Black	UL94V-0
	Shield	Stainless steel	Nickel plated	—
	Lock spring	Stainless steel	—	—
	Button	Polycarbonate resin	Black	UL94V-0
	Tapping screw	Steel	Black chromate(Cr+3)	—
Lock screw (DH-LNA***)	Screw lock	Steel	Nickel plated	—
	Waher	Steel	Nickel plated	—
	Spring washer	Steel	Nickel plated	—
Metal clamp(DH-CMB(**))	Metal clamp	Brass	—	—

Screw lock type


■ Receptacle connector

● Right angle type


[17pos. DH60-17P]




[27pos. DH60-27P]



[37pos. DH60-37P]





[51pos. DH60-51P]




● **Straight type**

[27pos. DH80-27P]




■Lock screw


[Applicable panel thickness 1.4 to 1.6mm:DH-LNA]




[Applicable panel thickness 0.9 to 1.2mm:DH-LNA-W4]



[Applicable panel thickness 0.5 to 0.8mm:DH-LNA-W8]



[No panel:DH-LNA-W16]



■Cover case


●Screw lock

[17pos. DH-17-CV1B]




Note 1. This product is delivered separately.


- ② A recommended screw tightening torque to lock screw(DH-LNA***) should be from 0.06 to 0.07N·m.
- ③ A recommended screw tightening torque for covers to be from 0.1 to 0.15N·m.




[27pos. DH-27-CV1B]



[37pos. DH-37-CV1B]



[51pos. DH-51-CV2B]




●Hand screw

[17pos. DH-17-CV2B]




Note 1. This product is delivered separately.

- ② A recommended screw tightening torque to the lock screws to be from 0.06 to 0.07N·m.
- ③ A recommended screw tightening torque for covers to be from 0.1 to 0.15N·m.




*Available in the near future

[27pos. DH-27-CV2B]




*Available in the near future

[37pos. DH-37-CV2B]



*Available in the near future

[51pos. DH-51-CV2B]




*Available in the near future

One Touch Lock Type


■ Receptacle connector

● Right angle type


[17pos. DH60A-17P]





[27pos. DH60A-27P]



[37pos. DH60A-37P]





■Cover case






●Metal button type

[17pos. DH-17-CT1B]







Note 1. This product is delivered separately.


② A recommended screw tightening torque for covers to be from 0.1 to 0.15N·m.




[27pos. DH-27-CT1B]




[37pos. DH-37-CT1B]



[51pos. DH-51-CT1B]




●Plastic button type
 [17pos. DH-17-CT2B]





Note 1. This product is delivered separately.


② A recommended screw tightening torque for covers to be from 0.1 to 0.15N·m.




[27pos. DH-27-CT2B]



[37pos. DH-37-CT2B]



[51pos. DH-51-CT2B]






■ Plug unit

● IDC type

[17pos. DH30B-17S]






Bundled parts



[27pos. DH30B-27S, DH30B-27S]



Bundled parts






*DH30B-27S and DH32B-27S are different holes in the attached parts.

[37pos. DH30B-37S]






Bundled parts



[51pos. DH30B-51S]




Bundled parts




●Solder contact type

[27pos. DH40-27S]




[37pos. DH40-37S]




■Metal clamp


[17pos. DH-17-CMB(6.3)]
(Cable outer diameter 6.3mm)




[27pos. DH-27-CMB(6.9)]
(Cable outer diameter 6.9mm)




[27pos. DH-27-CMB(7.3)]
(Cable outer diameter 7.3mm)



[37pos. DH-37-CMB(8.8)]
(Cable outer diameter 8.8mm)




[51pos. DH-51-CMB(9.6)]
(Cable outer diameter 9.6mm)




■Recommended PCB Mounting pattern


●DH60-***P, DH60A-***P



●DH80-27P




●DH80A-27P



■Terminal No.chart

●DH60-***P, DH60A-***P




■Panel cutout

●Screw lock type

Panel cutout for reference (Right angle type, Straight type)

(The dimension is specified based on the center of the connector interface)

DH-LNA(CL244-0045-0-00)




*Please set piercing R as less than R1.

DH-LNA-W4(CL244-0046-2-00)

DH-LNA-W8(CL244-0004-2-00)

DH-LNA-W16(CL244-0005-5-00)



*Please set piercing R as less than R1.

A·B·C·D dimension table


Unit:mm

Number of contacts	A	B	C	D
17	19.2	13.7	22	15
27	24.2	18.7	27	20
37	29.2	23.7	32	25
51	36.2	30.7	39	32

Connector mounted on PCB

(For example, panel thickness is 1.6mm)

*The drawing is shown sample of DH60-27P.




*An attachment to the panel needs screws shown in the table below.

Applicable panel thickness(mm)	Part No.	Code No.
1.4 to 1.6	DH-LNA	244-0045-0-00
0.9 to 1.2	DH-LNA-W4	244-0046-2-00
0.5 to 0.8	DH-LNA-W8	244-0004-2-00
No panel	DH-LNA-W16	244-0005-5-00

*The recommended screw tightening torque to be from 0.12 to 0.3 N·m


*DH80-27P



●One Touch Lock Type

Panel cutout for reference (Right angle type, Straight type)

(The dimension is specified based on the center of the connector interface)



*Please set piercing R as less than R1.


A·B dimension table

Unit:mm


Number of contacts	A	B
17	23.5	18
27	28.5	23
37	33.5	28
51	40.5	35

Connector mounted on PCB


*DH60A-27P is representative examples.




*SCREW FOR INSTALATION



*DH80A-27P



*SCREW FOR INSTALATION



■Applicable tools

	Process	Part No.	CL No.
1	Cable end processing	manual work	
2	Upper level wire arranging	wire arranging tool : DH/CA-MO	CL902-2183-0
3	Upper level press fitting		
4	Lower level wire arranging		
5	Lower level press fitting		
6	Cable cutting	manual work(nipper etc.)	
7	IDC	① IDC-clamping tool:DH/IDCK-MP	CL902-2185-5
		② attachment for 17pos:DH-17UNIT	CL902-2186-8
		attachment for 27pos:DH-27UNIT	CL902-2187-0
		attachment for 37pos:DH-37UNIT	CL902-2188-3
		attachment for 51pos:DH-51UNIT	CL902-2189-6
		③ HI-FLEX termination press (Select appropriate attachment of each pin count from ②.)	CL550-0082-2
8	Cable clamping	① IDC-clamping tool:DH/IDCK-MP	CL902-2185-5
		② attachment for DH-17-CMB(6.3):DH-17-CMB(6.3)UNIT	CL902-2190-5
		attachment for DH-27-CMB(6.9):DH-27-CMB(6.9)UNIT	CL902-2194-6
		attachment for DH-27-CMB(7.3):DH-27-CMB(7.3)UNIT	CL902-2191-8
		attachment for DH-37-CMB(8.8):DH-37-CMB(8.8)UNIT	CL902-2192-0
		attachment for DH-51-CMB(9.6):DH-51-CMB(9.6)UNIT	CL902-2193-3
		③ HI-FLEX termination press (Select appropriate attachment of each pin count from ②.)	CL550-0082-2
9	Cover attaching	manual work(torque driver etc.)	

*Customers already having HI-FLEX termination press can apply it to this product assembly.

*Each ① and ③ of 7. IDC and 8. Clamping are the same tools. All the parts ①, ② and ③ are required for each 7. IDC and 8.

Clamping processes for mass-production.