

Use recommendations for machines

The realisation of a printed circuit needs many equipments, products and accessories... Your choice will be first based on technical and then financial criterias thanks to available budget. Taking care of our wide range of equipments and products, the following pages have been created to advise the user the best possible.



	Article code	Hobby	1 face	2 faces	Metallised 2 faces		Article code	Hobby	1 face	2 faces	Metallised 2 faces
SINGLE SIDED EXPOSURE UNITS						ETCHING MACHINES 2 F					
Working area 160 x 260 mm, "hobby" model	DP42	●				Working area 200 x 300 mm, GR 2030 model	DP36	●		●	
Working area 180 x 400 mm, «kits»-fitting model	BC6	●	●			Working area 240 x 340 mm, GR 2434 model	DP37	●		●	
Working area 180 x 400 mm, Fully assembled model	BC10		●			Working area 200 x 300 mm, GIROJET 2 model	DP9	●		●	
Working area 254 x 405 mm, MI 10-16 model	BC4		●			Working area 300 x 300 mm, GIROJET R3 model	DP10	●		●	
Working area 235 x 400 mm, SFE 2340 model	DP 136		●			Working area 250 x 8 mm, AUTOJET model	DP86/88/90	●		●	●
Working area 300 x 400 mm, SFT 3040 model	DP 39		●			Working area 300 x 8 mm, GTA 300 model	DP13	●		●	●
DOUBLE SIDED UV-EXPOSURE UNITS						HIGH SPEED DRILLING MACHINE					
Working area 235 x 400 mm, DP 134 model	DP134		●	●		DS 115 model	DS115	●	●	●	
Working area 300 x 400 mm, DFT 3040 model	DP40		●	●	●	DS 140 model	DP140	●	●	●	
Working area 400 x 500 mm, CSV 4050 model	DP3		●	●	●	TECHNO 007 MR model	DP593		●	●	
Working area 500 x 600 mm, CSV 5060 model	DP4		●	●	●	TECHNO 010 model	EP501		●	●	●
ETCHING MACHINES 1 F						PC CONTROLLED 3 AXES DRILLING CUTTING MACHINES					
Working area 180 x 280 mm, "hobby" model	DP41	●				TECHNODRILL model	C11000		●	●	●
Working area 180 x 240 mm, GRAV'CI 2 model	BB2			●							
Working area 180 x 240 mm, GRAV'CI 2, 48V model	BB28			●							
Working area 270 x 410 mm, GRAV'CI 3 model	BB3			●							
Working area 270 x 410 mm, GRAV'CI 3, 48V model	BB38			●							
Working area 200 x 300 mm, GIROJET 1 model	DP8			●							
ETCHING MACHINES 2 F											
Working area 200 x 300 mm, BB 4 model	BB4		●	●							
Working area 200 x 300 mm, 48 Volts, BB 48 model	BB48		●	●							