

Visual Signals STATIC FILAMENT

BEACONS





Industrial Flashing Filament Beacons > SF125 DIN & SFA125 Series

Product overview

Suitable for fire, security & light industrial applications, these beacons are of the Static Mode type. Once the unit is energised the lamp will stay permanently ON - often referred to as Steady Mode. The SFA version incorporates

two Piezo sounders situated in the base that are synchronised to the flash rate. An M12 sealing gromet in the base allows for cable entry and termination inside the enclosure. The main advantage of these units is that the flash rate can be controlled by an exterior source i.e. a control panel.



Features

- Continuously rated
- Combined audible & visual signal
- 360° visibility
- Cage guard option available - see accessory page
- 3 Point fix

Material

- UV Stable Polycarbonate Lens
- UV Stable ABS Plastic Base



Code No:	Voltage:	Light Source:	Current:
SF125-90	12v Dc ---	Ba15d x 21w	1.75 A
SF125-91	24v Dc ---	Ba15d x 21w	0.88 A
SF125-92	115v Ac ~	Ba15d x 15w	0.13 A
SF125-93	230v Ac ~	Ba15d x 15w	0.07 A
For Audible Option			
SFA125-80	12v Dc ---	Ba15d x 21w	1.80 A
SFA125-81	24v Dc ---	Ba15d x 21w	0.90 A
SFA125-82	115v Ac ~	Ba15d x 15w	0.15 A
SFA125-83	230v Ac ~	Ba15d x 15w	0.08 A

Kg 0.25

50/60 Hz

°C -25+55

IP 65

dB 90

INDUSTRIAL

APPROVAL AND CONFORMITIES



ADD THE FOLLOWING LENS CODES TO THE PRODUCT CODE WHEN ORDERING

