



LOCTITE[®] 7061[™]

June 2010

PRODUCT DESCRIPTION

LOCTITE[®] 7061[™] provides the following product characteristics:

Technology	Solvent based
Appearance	Transparent, colorless liquid ^{LMS}
Solvent	Acetone / Alcohol*
Cure	Not applicable
Application	Surface preparation
Specific Benefit	<ul style="list-style-type: none"> • Non-corrosive • Alternative to 1,1,1 Trichloroethane

LOCTITE[®] 7061[™] is a non-CFC solvent based formulation for cleaning and degreasing of surfaces to be bonded with LOCTITE[®] adhesives. The product is used as a final pre-assembly cleaning treatment to remove most greases, oils, lubrication fluids, metal cuttings and fines from surfaces to be bonded. Its high solvent power allows it to be very effective in other degreasing or part-cleaning applications.

TYPICAL PROPERTIES

Specific Gravity @ 25 °C	0.8
Flash Point - See MSDS	
Viscosity @ 20°C, mPa·s (cP)	2.0
Infrared Spectroscopy	To match standard ^{LMS}
Drying Time @ 20 °C, seconds	60
TLV (ACGIH), ppm	813

TYPICAL PERFORMANCE

LOCTITE[®] 7061[™] has no effect on the speed of cure or final strength of LOCTITE[®] adhesives other than providing a clean surface for good adhesion and adhesive cure. Unclean or partially cleaned surfaces can affect adhesive performance.

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Handling precautions

Cleaner must be handled in a manner applicable to highly flammable materials and in compliance with relevant local regulations. Special care must be taken to avoid contact of the product or its vapour with naked flame or any electrical equipment that is not flame proofed.

The solvent can affect certain plastics or coatings. It is recommended to check all surfaces for compatibility before use.

Directions for use:

1. Treat surfaces to be bonded by generously spraying with LOCTITE[®] 7061[™].
2. Wipe surfaces when still wet with a clean cloth to remove all heavy contamination. If necessary, spray surfaces again to allow run-off of product.
3. Spray surfaces again, preferably with surfaces in vertical position to allow run-off of the cleaner.
4. Allow LOCTITE[®] 7061[™] to fully evaporate from parts prior to bonding to avoid solvent entrapment within the bond joint.
5. Apply the Loctite[®] adhesive immediately after drying and assemble bond.

Loctite Material Specification^{LMS}

LMS dated September 01, 1995. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

Storage

The product is classified as flammable and must be stored in an appropriate manner in compliance with relevant regulations. Do not store near oxidizing agents or combustible materials. Store product in the unopened container in a dry location. Storage information may also be indicated on the product container labelling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
kV/mm \times 25.4 = V/mil
mm / 25.4 = inches
 $\mu\text{m} / 25.4 = \text{mil}$
N \times 0.225 = lb
N/mm \times 5.71 = lb/in
N/mm² \times 145 = psi
MPa \times 145 = psi
N·m \times 8.851 = lb·in
N·m \times 0.738 = lb·ft
N·mm \times 0.142 = oz·in
mPa·s = cP

Note

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.2