




PART NO.

MCBFS5220-470KU


REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	ASK	20/4/11	SID	20/4/11		04/5/11


Configurations and Dimensions




Top View



Side View



Bottom View




Suggest PCB Layout

Dimensions : Millimetres

A	12.95 mm	(Max.)
B	9.5 mm	
C	5.2 mm	
D	8.4 ± 0.3 mm	-
E	7.62 mm	(Ref.)
F	2.54 mm	
G		

Schematic Diagram



Note:

1. Wire Ø0.16mm × 1P 2UEWF 155°C
2. 42.5TS (Reference)



Marking : 470

Electrical Characteristics (at 25°C)

Test Condition		
100 KHz 0.1 V	L	47 µH ±10%
at 25°C	DCR	500 mΩ (Max.)
100 KHz 0.1 V I <sub>rms</sub> = 1.29 A	L at I <sub>rms</sub>	ΔT 40°C (Max.)

Operating temperature : -55°C to +130°C

Note : I<sub>rms</sub> : Temperature rise 40°C

Test Data for Mechanical

Test Item	A mm	B mm	C mm	D mm	E mm	F mm	G mm
Specification	12.95 (Max.)	9.5 (Max.)	5.2 (Max.)	8.4 ±0.3	7.62 (Ref.)	2.54 (Ref.)	2.54 (Ref.)
1	12.78	9.2	4.81	8.5	7.62	2.52	2.53
2	12.75	9.22	4.8	8.48	7.6	2.51	2.52
3	12.78	9.23	4.81	8.51	7.61	2.53	2.53
4	12.8	9.18	4.78	8.52	7.62	2.5	2.51
5	12.76	9.2	4.79	8.49	7.59	2.52	2.52
<b>Average</b>	<b>12.77</b>	<b>9.21</b>	<b>4.8</b>	<b>8.5</b>	<b>7.61</b>	<b>2.52</b>	<b>2.52</b>

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

ASK

CHECKED BY:

SID

APPROVED BY:

DATE:

20/04/11

DATE:

20/04/11

DATE:

04/05/11

DRAWING TITLE:

**Inductor**

SIZE  
**A**

DWG NO.

**M10003467**

ELECTRONIC FILE

MCBFS5220-470KU

REV

**A**

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 4





PART NO.

MCBFS5220-470KU

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	ASK	20/4/11	SID	20/4/11		04/5/11

Electric Characteristics



Test Data for Electrical

Test Item	L µH	DCR mΩ	L at I <sub>rms</sub> µH
Condition	100 KHz 0.1 V	at 25°C	100 KHz 0.1 V I <sub>rms</sub> = 1.29 A
Specification	47 ±10%	500 (Max.)	ΔT 40°C (Max.)
1	47.85	415.6	OK
2	47.93	410.6	
3	48.16	412.3	
4	48.56	415.2	
5	47.24	414.3	
Average	47.95	413.6	OK

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASK	20/04/11
CHECKED BY:	DATE:
SID	20/04/11
APPROVED BY:	DATE:
	04/05/11

DRAWING TITLE:

**Inductor**

SIZE <b>A</b>	DWG NO. <b>M10003467</b>	ELECTRONIC FILE MCBFS5220-470KU	REV <b>A</b>
SCALE: NTS	U.O.M.: mm	SHEET: 2 OF 4	



PART NO.

MCBFS5220-470KU

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	ASK	20/4/11	SID	20/4/11		04/5/11

Reliability Test

Test Item	Specifications	Test Method and Remarks
Solderability	The electrodes shall be at least 90% covered with new solder coating.	According to IEC68-2-20 Soldering temperature : 245 ±5°C Solder : Sn99.3% / Cu0.7% Flux : Rosin Immersion time : 5 ±1 s
Soldering heat resistance	Appearance : No damage Inductance change : Within ±10% of initial value	Preheat temperature 150°C Preheat time : 1 min Solder temperature : 260 ±5°C Dipping time : 10 ±1 s Measured at room temperature after placing for 24 hours.
Vibration (Out LAB)	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to MIL-STD202 Method 204 Frequency : 10 to 55 Hz Amplitude : 1.52 mm Direction and time X Y and Z direction for 2 hours each.
Humidity resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-1 Method Ca Temperature : 40 ±2°C Humidity : 90%-95% RH Test time : 500 ±2 hrs The component should be stabilized at normal condition for 24 hours before test.
High temperature resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-2 Temperature : 85 ±3°C Test time : 500 +24 hrs The component should be stabilized at normal condition for 24 hours before test.
Low temperature resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-1 Method A (Ad) Temperature : -40 ±3°C Test time : 500 +24 hrs The component should be stabilized at normal condition for 24 hours before test.
Temperature cycles test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-14 Method N (Nb) High-temperature : 85 ±3°C duration 30 mins Room-temperature : 25 ±2°C duration 3 hrs Low-temperature : -40 ±3°C duration 30 mins Room-temperature : 25 ±2°C duration 3 hrs Number of cycle : 10 cycles The component should be stabilized at normal condition for 24 hours before test.

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASK	20/04/11
CHECKED BY:	DATE:
SID	20/04/11
APPROVED BY:	DATE:
	04/05/11

DRAWING TITLE:			
<b>Inductor</b>			
SIZE	DWG NO.	ELECTRONIC FILE	REV
A	M10003467	MCBFS5220-470KU	A
SCALE: NTS		U.O.M.: mm	SHEET: 3 OF 4



PART NO.

MCBFS5220-470KU

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	ASK	20/4/11	SID	20/4/11		04/5/11

Material List

No.	Item	Material Description
1	Core	R5A DR4.8 × 4 R5A RI 8.4 × 4.1 × 6.85
2	Wire	Ø0.16 mm × 1P 2UEWF (155°C)
3	Solder (Lead-free)	Sn99.3% / Cu0.7%
4	Glue	TH320D / TH320-3
5	Base	SN-BS019.01 LCP

Part Number Table

Description	Part Number
Inductor, 47µH, 10%, SMD	MCBFS5220-470KU

<http://www.element14.com>

<http://www.farnell.com>

<http://www.newark.com>

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASK	20/04/11
CHECKED BY:	DATE:
SID	20/04/11
APPROVED BY:	DATE:
	04/05/11

DRAWING TITLE:

**Inductor**

SIZE <b>A</b>	DWG NO. <b>M10003467</b>	ELECTRONIC FILE MCBFS5220-470KU	REV <b>A</b>
SCALE: NTS	U.O.M.: mm	SHEET: 4 OF 4	