

PSR 7.2 LI



Lithium-ion Cordless Screwdriver

PSR 7.2 LI

Lithium-ion technology – Small, lightweight and powerful for all screwdriving work

- **No self-discharge, no memory effect: always ready for use thanks to lithium-ion technology**
- **Always the right power: 10 pre-selectable torque settings, forward/reverse indicator and charge level indicator**
- **Particularly long life of the lithium-ion cells due to Bosch Electronic Cell Protection (ECP)**



Lithium-ion technology



Forward/reverse indicator, battery charge level indicator and torque setting



Charging station

- Automatic spindle lock for manual tightening or loosening of screws
- PowerLight – thanks to the built-in LED, your workpiece is always well lit and clearly visible
- Softgrip for a better and more comfortable hold
- Optimum storage in the charging station

Part no. 0 603 957 770

- 3-hour lithium-ion charging station
- Bit set holder with 10 bits
- Plastic case

Technical data

Screw diameter up to	6 mm
No-load speed	240 rpm
Max. torque for soft/hard screwdriving applications	6 / 10 Nm
Battery voltage	7,2 V
Charging time	5 h
Chucks	Magnetic bit holder with hexagonal shank
Torque settings	10

Functions

- 7.2 Volt
- Lithium-ion technology
- Bosch Electronic Cell Protection (ECP)
- Power Control
- Application: screwdriving
- Softgrip
- Integrated work light
- Bosch Electronic
- Forward/reverse rotation
- Charge level indicator
- Forward/reverse indicator

Noise/vibration information

Show values

Measured values determined according to EN 60745
Total vibration values (vector sum of three directions)

Screwdriving

Vibration emission value ah 2,5 m/s²

Uncertainty K 1,5 m/s²

The A-rated noise level of the power tool is typically as follows: Sound pressure level 70 dB(A); Sound power level 80 dB(A). Uncertainty K= 3 dB.

