

## EVERCRYL ONE COAT



Colour	Product Code	Pack Size	Box Qty
Grey	EVCGY01	1Kg	12
	EVCGY02	2.5Kg	6
	EVERYL5GY	5Kg	4
	EVCGY20	20Kg	1
Black	EVCBK02	2.5Kg	6
	EVCBK5	5Kg	4
White	EVCWE5	5Kg	4

### Product Description

EVERCRYL ONE COAT is a resin based, fibre re-enforced roof repair compound which is effective on all common roofing surfaces and types, giving an instant roof repair even in the wet and on wet surfaces. May also be applied in frosty conditions down to  $-5^{\circ}\text{C}$ . EVERCRYL ONE COAT is instantly waterproof when applied, so there is no fear of wash off, so emergency leaks can be tackled immediately as there is no need to wait for the rain to stop. EVERCRYL ONE COAT is brush applied and dries to a smooth seamless flexible membrane which resists algae and fungal growth. Because of the high level of fibre re-enforcement, EVERCRYL ONE COAT will bridge small cracks and requires only a one-coat brush application to give instant and total water protection, even in areas subject to ponding. EVERCRYL ONE COAT requires no primer on sound non-porous surfaces.

### Benefits

- May be applied in damp and wet conditions.
- Formulated from lightfast acrylic polymers to withstand sunlight for longer periods than traditional bitumen coatings
- Fibre re-enforced to bridge small cracks.
- Primerless adhesion to most bituminous and non porous surfaces.

### Areas For Use

- General sealing, maintenance, repair and waterproofing of most common roofs in wet or dry conditions— for use on concrete, fibre/cement, roofing felt, mastic asphalt, existing bituminous roof coatings, rigid uPVC corrugated iron, metals, slates, brickwork, tiles, lead, copper and zinc.
- Waterproofing guttering (plastic and metal), downpipes, gully's, flashings, upstands, vents and leadwork.

### Limitations

Do not use in areas where subsequent solvent or oil contact is likely.. Avoid inhalation of vapours. Do not use on Styrofoam or PVC foil. As the manufacturer cannot know all the uses its products may be put to, it is the users responsibility to determine suitability for use. If in doubt, contact technical services department for advice.

### Surface Preparation

No roof-coating product can be expected to repair an existing roof that is not structurally sound and stable. Before using a surface coating the roof structure should be inspected and, if necessary, put in order. All cracked, broken, slipped or missing slates, tiles, sheets or other forms of covering should be replaced or re-fixed and cracks in felt or asphalt filled. (Safety Recommendation: do not coat roof lights, windows, glass or translucent sheets. These will constitute a hidden hazard if disguised).

Preparation of the surface is of great importance and will influence the degree of adhesion and life of the renovation. All roof surfaces to be coated should be sound, stable, clean, i.e. free from loose debris, dirt, dust and grease. All traces of algae and fungi growth should be removed using a stiff-bristled brush. Where algae and fungi have been present, remove them completely and treat the surface with EVERBUILD MOSS AND MOULD REMOVER to kill any remaining spores, thereby discouraging the return of the growths.

Make good any holes or loose felt/slates/tiles etc. Fill holes/imperfections with BLACK JACK BITUMEN MASTIC. Stick down loose felt etc with BLACK JACK ROOF FELT ADHESIVE. Blisters in roofing felt must be cut, dried, re-bonded and sealed. New metal surfaces must be degreased with a suitable solvent. Remove all rust or treat rusty surfaces with a rust inhibitive primer (eg zinc phosphate based). All non-bituminous, porous or friable surfaces must be primed with BLACK JACK BITUMEN AND FLASHING PRIMER allowing primer to dry thoroughly before use.

#### Application

Wear gloves and suitable face/eye protection. Flammable product - eliminate all sources of ignition STIR WELL BEFORE USE. Apply by brush in a one coat at a rate of 1-2 litres per square meter. In extreme cases, a second coat may be applied 2-3 days after initial application.

#### Specific Data

<b>Chemical Base</b>	Modified acrylic re-enforce with Dralon fibres in solvent blend
<b>Viscosity</b>	Brushable paste
<b>Character</b>	Elasto-plastic
<b>Elongation</b>	500% at break
<b>Density</b>	1.05 g/cm <sup>3</sup>
<b>Auto Ignition Temp</b>	420°C
<b>Curing Method</b>	Via solvent loss and physical drying
<b>Application Temps</b>	-5 to + 35°C
<b>Service Temps</b>	-25 to + 100°C
<b>Storage Temps</b>	Do not exceed 60°C. Will withstand frost.
<b>Drying Time</b>	24-48 hours per coat, product is however instantly rain and frostproof.
<b>Coverage</b>	1-2 litres / square meter
<b>Cleaning</b>	Tools, brushes etc with brush cleaner or white spirits.

#### Health & Safety

Consult MSDS for full list of hazards.

#### Storage

Store in cool dry conditions away from all sources of ignition

#### Shelf Life

Storage life 12 months in tightly sealed undamaged containers. When stored between 5 and 25°C

*The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.*