

**MATERIAL / FINISHS**

<b>INSULATOR</b>	Material	P.B.T & GLASS FILL REINFORCED UL-94V-0
<b>CONTACT</b>	Material	BRASS
	Plating	TIN PLATED OVER NICKEL
	Thickness	TIN: 80~100u" BASE NICKEL: 40u"
<b>SHELL</b>	Material	NO
	Plating	NO
	Thickness	NO
<b>SCREWLOCK, BOARDLOCK, RIVET, GROUNDING.</b>	Material	NO

**SPECIFICATION**


<b>RATE CURRENT</b>	3 AMP.
<b>INSULATION RESISTANCE</b>	3000 MEGOHM MIN. AT 500V DC
<b>CONTACT RESISTANCE</b>	15 MILLIOHM MAX
<b>DIELECTRIC WITHSTANDING VOLTAGE</b>	1000 V AC / 1 MINUTE
<b>OP. TEMPERATURE</b>	-55°C ~ +105°C

**REMARKS:**

**G18FA SERIES**

DIVISION STAMP	APPROVED	CHECKED	DRAWN
	<i>Jen</i> 3/5	<i>Jen</i> 3/5	Candy3/5

BDC-0375-1	BDC-0376-1	BDC-0377-1	BDC-0378-1	BDC-0379-1	BDC-0380-1
MINI 3P	MINI 4P	MINI 5P	MINI 6P	MINI 7P	MINI 8P





PART NO	PIN	MATERIAL	REMARK
E	PIN	BRASS	AG PLATING
D	PLASTIC CONNECTOR	PC	
C	SHELL	BRASS	NI PLATING
B	MIDDLE SLEEVE	ABS	
A	OUTER SLEEVE	PVC	


MINI DIN  
ASSEMBLY TYPE  
RECEPTACLE

REV	DATE	DESCRIPTION
B	03/29/01	
A	04/24/88	

UNLESS OTHERWISE SPECIFIED TOLERANCE	0.1	0.05	0.02
SCALE AS SHOWN	UNIT: MM		
DRAWN	CHECKED	DATE	
JOE	Joe	04/02/01	
APPROVED	DATE	PRODUCT NO.	
	04/03/01	G18FA0 X 0350	
DATE	REV	FILE NUMBER	
04/03/01	A4	B	



ASSEMBLY TYPE MALE



UNLESS OTHERWISE SPECIFIED TOLERANCES		DRAWN NAME:	
0.5	±0.5	DATE	04/24/98
0.3	±0.3	CHECKED	ROSIE
.00	±0.2	APPROVED	<i>[Signature]</i>
SCALE: 1:1	UNIT: MM	DATE	04/24/98
DRAWN: ROSIE		DATE	04/24/98
DRAWN NAME:		DATE	04/24/98
MINI DIN SOLDER TYPE		DATE	04/24/98
PRODUCT NO: G18FA 0X 1350		DATE	04/24/98
FILE NAME:		DATE	04/24/98
DESCRIPTION		DATE	04/24/98
REV. A		DATE	04/24/98
REV.		DATE	04/24/98