

9991 Multi-Conductor - Audio, Control and Instrumentation Cable

For more Information
please call

1-800-Belden1



Description:

24 AWG stranded (7x32) TC conductors, polyethylene insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 24 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
6	24	7x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
PE - Polyethylene

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 8.382 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown

Pair Lay Length & Direction:

Lay Length (mm)
44.449825

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

METRIC MEASUREMENT VERSION

9991 Multi-Conductor - Audio, Control and Instrumentation Cable

UL Temperature Rating: 80°C (UL AWM Style 2919)

Bulk Cable Weight: 92.268 Kg/Km

Min. Bend Radius (Install)/Minor Axis: 88.900 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

AWM Specification: UL Style 2919 (30 V 80°C)

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

60

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

82.025

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

154.207

Nominal Velocity of Propagation:

VP (%)

66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

78.744

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 59.058 Ohm/km

Max. Operating Voltage - UL:

Voltage

30 V RMS (UL AWM Style 2919)

300 V RMS

Max. Operating Voltage - Non-UL:

Voltage Description

300

Max. Recommended Current:

Current

9991 Multi-Conductor - Audio, Control and Instrumentation Cable

1.1 Amps per conductor @ 25°C (10°C rise in temp)

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9991 060100	30 MT	3.039 KG	CHROME		6 FS PR #24 PE PVC
9991 0601000	305 MT	28.123 KG	CHROME	C	6 FS PR #24 PE PVC
9991 060500	152 MT	14.742 KG	CHROME	C	6 FS PR #24 PE PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-18-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.