


5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information
please call

1-800-Belden1



Description:

16 AWG bare copper conductors, PP insulation, conductors cabled, Beldfoil® shield tape (foil side out) with drain wire, PVC jacket with ripcord, sequential footage marking every two feet

Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	16	19x29	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.178

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.432

Outer Jacket Ripcord: Yes

Overall Cabling

Overall Cabling Lay Length & Direction:

Length (mm)	Twists (m.)
76.1997	1.2192

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 4.572 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 44.795 Kg/Km

Max. Recommended Pulling Tension: 380.321 N

5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Min. Bend Radius (Install)/Minor Axis:	45.720 mm
--	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
-------------------------	-----

NEC Articles:	800
---------------	-----

CEC/C(UL) Specification:	CMG
--------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

C(UL) Flame Test:	FT4
-------------------	-----

Plenum/Non-Plenum

Plenum Number:	6200FE
----------------	--------

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)

0.459

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

207.523

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

374.034

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

13.124

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

47.246

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

6.25 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

5200FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5200FE 008U1000	305 MT	14.061 KG	GRAY		2 #16 PP FS FRPVC
5200FE 008U500	152 MT	6.124 KG	GRAY		2 #16 PP FS FRPVC
5200FE 0081000	305 MT	11.793 KG	GRAY	C	2 #16 PP FS FRPVC
5200FE 008500	152 MT	6.124 KG	GRAY	C	2 #16 PP FS FRPVC
5200FE 009U1000	305 MT	14.061 KG	WHITE		2 #16 PP FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-02-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.